

HPLC Columns




Cat#	Product	Pack Size	INR Price
Fused Core - Ascentis Express HPLC Columns			
53802-U	Ascentis Express C18, 3 cm x 2.1 mm, 2.7 µm	1 ea	16,392
53822-U	Ascentis Express C18, 5 cm x 2.1 mm, 2.7 µm	1 ea	22,243
53823-U	Ascentis Express C18, 10 cm x 2.1 mm, 2.7 µm	1 ea	28,104
53818-U	Ascentis Express C18, 3 cm x 4.6 mm, 2.7 µm	1 ea	16,392
53826-U	Ascentis Express C18, 5 cm x 4.6 mm, 2.7 µm	1 ea	22,243
53827-U	Ascentis Express C18, 10 cm x 4.6 mm, 2.7 µm	1 ea	28,104
53829-U	Ascentis Express C18, 15 cm x 4.6 mm, 2.7 µm	1 ea	32,544
53831-U	Ascentis Express C8, 5 cm x 2.1 mm, 2.7 µm	1 ea	22,243
53832-U	Ascentis Express C8, 10 cm x 2.1 mm, 2.7 µm	1 ea	28,104
53836-U	Ascentis Express C8, 5 cm x 4.6 mm, 2.7 µm	1 ea	22,243
53837-U	Ascentis Express C8, 10 cm x 4.6 mm, 2.7 µm	1 ea	28,104
53934-U	Ascentis Express HILIC, 5 cm x 2.1 mm, 2.7 µm	1 ea	22,449
53939-U	Ascentis Express HILIC, 10 cm x 2.1 mm, 2.7 µm	1 ea	28,357
53975-U	Ascentis Express HILIC, 5 cm x 4.6 mm, 2.7 µm	1 ea	21,382
53979-U	Ascentis Express HILIC, 10 cm x 4.6 mm, 2.7 µm	1 ea	28,357
53981-U	Ascentis Express HILIC, 15 cm x 4.6 mm, 2.7 µm	1 ea	32,842
Ascentis HPLC Columns			
581300-U	Ascentis C18, 5 cm x 2.1 mm, 3 µm	1 ea	16,255
581301-U	Ascentis C18, 10 cm x 2.1 mm, 3 µm	1 ea	17,562
581303-U	Ascentis C18, 5 cm x 2.1 mm, 5 µm	1 ea	16,255
581326-U	Ascentis C18, 10 cm x 2.1 mm, 5 µm	1 ea	17,562
581323-U	Ascentis C18, 5 cm x 4.6 mm, 5 µm	1 ea	16,255
581324-U	Ascentis C18, 15 cm x 4.6 mm, 5 µm	1 ea	19,650
581325-U	Ascentis C18, 25 cm x 4.6 mm, 5 µm	1 ea	20,488
565323-U	Ascentis RP-Amide, 5 cm x 4.6 mm, 5 µm	1 ea	16,255
565324-U	Ascentis RP-Amide, 15 cm x 4.6 mm, 5 µm	1 ea	19,650
565325-U	Ascentis RP-Amide, 25 cm x 4.6 mm, 5 µm	1 ea	20,488
581424-U	Ascentis C8, 15 cm x 4.6 mm, 5 µm	1 ea	19,650
581425-U	Ascentis C8, 25 cm x 4.6 mm, 5 µm	1 ea	20,488
581511-U	Ascentis HILIC, 5 cm x 4.6 mm, 5 µm	1 ea	16,255
581512-U	Ascentis HILIC, 15 cm x 4.6 mm, 5 µm	1 ea	19,650
581513-U	Ascentis HILIC, 25 cm x 4.6 mm, 5 µm	1 ea	20,488
581615-U	Ascentis Phenyl, 5 cm x 4.6 mm, 5 µm	1 ea	16,255
581616-U	Ascentis Phenyl, 15 cm x 4.6 mm, 5 µm	1 ea	19,650
581617-U	Ascentis Phenyl, 25 cm x 4.6 mm, 5 µm	1 ea	20,488
Discovery HPLC Columns			
504947	Discovery C18, 5 cm x 4.6 mm, 5 µm	1 ea	20,132
504955	Discovery C18, 15 cm x 4.6 mm, 5 µm	1 ea	29,079
504971	Discovery C18, 25 cm x 4.6 mm, 5 µm	1 ea	31,316
568520-U	Discovery HS18, 5 cm x 4.6 mm, 5 µm	1 ea	20,132
568522-U	Discovery HS18, 15 cm x 4.6 mm, 5 µm	1 ea	27,691
568523-U	Discovery HS18, 25 cm x 4.6 mm, 5 µm	1 ea	31,316
505013	Discovery RP-Amide, 15 cm x 4.6 mm, 5 µm	1 ea	29,079
505064	Discovery RP-Amide, 25 cm x 4.6 mm, 5 µm	1 ea	31,316
567513-U	Discovery HS F5, 5 cm x 4.6 mm, 5 µm	1 ea	20,132
567516-U	Discovery HS F5, 15 cm x 4.6 mm, 5 µm	1 ea	29,079
567517-U	Discovery HS F5, 25 cm x 4.6 mm, 5 µm	1 ea	31,316

Note: All Prices in Indian Rupees. Taxes & other levies extra as applicable

Sigma Aldrich Chemicals Pvt. Ltd.

#12, Bommasandra-Jigani Link Road, Bangalore - 560 100
T +91 80 6621 9600 F +91 80 6621 9650 E india@sial.com

New Delhi +91 11 4358 8000 Kolkata +91 33 4013 8000 Mumbai +91 22 4087 2364
Lucknow +91 522 400 3455 Chennai +91 44 4214 8991 Pune +91 20 2553 9079
Chandigarh +91 172 463 0255 Hyderabad +91 40 4015 5488 Ahmedabad +91 79 2754 1971



For your free copy of
Supelco Catalog,
please write to
INDMarcom@sial.com

SIAL/ANV05/0710/INR