

Cat#	Product	Pack Size	Duty Free Price	Duty Paid Price
<b>Fused Core - Ascentis Express HPLC Columns</b>				
53802-U	Ascentis Express C18, 3 cm x 2.1 mm, 2.7 um	1 ea	13,610	16,195
53822-U	Ascentis Express C18, 5 cm x 2.1 mm, 2.7 um	1 ea	18,470	21,979
53823-U	Ascentis Express C18, 10 cm x 2.1 mm, 2.7 um	1 ea	23,330	27,762
53818-U	Ascentis Express C18, 3 cm x 4.6 mm, 2.7 um	1 ea	13,610	16,195
53826-U	Ascentis Express C18, 5 cm x 4.6 mm, 2.7 um	1 ea	18,470	21,979
53827-U	Ascentis Express C18, 10 cm x 4.6 mm, 2.7 um	1 ea	23,330	27,762
53829-U	Ascentis Express C18, 15 cm x 4.6 mm, 2.7 um	1 ea	27,020	32,153
53831-U	Ascentis Express C8, 5 cm x 2.1 mm, 2.7 um	1 ea	18,470	21,979
53832-U	Ascentis Express C8, 10 cm x 2.1 mm, 2.7 um	1 ea	23,330	27,867
53836-U	Ascentis Express C8, 5 cm x 4.6 mm, 2.7 um	1 ea	18,470	21,979
53837-U	Ascentis Express C8, 10 cm x 4.6 mm, 2.7 um	1 ea	23,330	27,762
53934-U	Ascentis Express HILIC, 5 cm x 2.1 mm, 2.7 um	1 ea	18,640	22,181
53939-U	Ascentis Express HILIC, 10 cm x 2.1 mm, 2.7 um	1 ea	23,540	28,012
53975-U	Ascentis Express HILIC, 5 cm x 4.6 mm, 2.7 um	1 ea	18,640	22,181
53979-U	Ascentis Express HILIC, 10 cm x 4.6 mm, 2.7 um	1 ea	23,540	28,012
53981-U	Ascentis Express HILIC, 15 cm x 4.6 mm, 2.7 um	1 ea	27,270	32,450
<b>Ascentis HPLC Columns</b>				
581300-U	Ascentis C18, 5 cm x 2.1 mm, 3 um	1 ea	13,500	16,065
581301-U	Ascentis C18, 10 cm x 2.1 mm, 3 um	1 ea	14,580	17,350
581303-U	Ascentis C18, 5 cm x 2.1 mm, 5 um	1 ea	13,500	16,065
581326-U	Ascentis C18, 10 cm x 2.1 mm, 5 um	1 ea	14,580	17,350
581323-U	Ascentis C18, 5 cm x 4.6 mm, 5 um	1 ea	13,500	16,065
581324-U	Ascentis C18, 15 cm x 4.6 mm, 5 um	1 ea	16,310	19,408
581325-U	Ascentis C18, 25 cm x 4.6 mm, 5 um	1 ea	17,010	20,241
565323-U	Ascentis RP-Amide, 5 cm x 4.6 mm, 5 um	1 ea	13,500	16,065
565324-U	Ascentis RP-Amide, 15 cm x 4.6 mm, 5 um	1 ea	16,310	19,408
565325-U	Ascentis RP-Amide, 25 cm x 4.6 mm, 5 um	1 ea	17,010	20,241
581424-U	Ascentis C8, 15 cm x 4.6 mm, 5 um	1 ea	16,310	19,408
581425-U	Ascentis C8, 25 cm x 4.6 mm, 5 um	1 ea	17,010	20,241
581511-U	Ascentis HILIC, 5 cm x 4.6 mm, 5 um	1 ea	13,500	16,065
581512-U	Ascentis HILIC, 15 cm x 4.6 mm, 5 um	1 ea	16,310	19,408
581513-U	Ascentis HILIC, 25 cm x 4.6 mm, 5 um	1 ea	17,010	20,241
581615-U	Ascentis Phenyl, 5 cm x 4.6 mm, 5 um	1 ea	13,500	16,065
581616-U	Ascentis Phenyl, 15 cm x 4.6 mm, 5 um	1 ea	16,310	19,408
581617-U	Ascentis Phenyl, 25 cm x 4.6 mm, 5 um	1 ea	17,010	20,241
<b>Discovery HPLC Columns</b>				
504947	Discovery C18, 5 cm x 4.6 mm, 5 um	1 ea	16,070	19,123
504955	Discovery C18, 15 cm x 4.6 mm, 5 um	1 ea	23,210	27,619
504971	Discovery C18, 25 cm x 4.6 mm, 5 um	1 ea	25,000	29,749
568520-U	Discovery HS18, 5 cm x 4.6 mm, 5 um	1 ea	16,070	19,123
568522-U	Discovery HS18, 15 cm x 4.6 mm, 5 um	1 ea	23,210	27,619
568523-U	Discovery HS18, 25 cm x 4.6 mm, 5 um	1 ea	25,000	29,749
505013	Discovery RP-Amide, 15 cm x 4.6 mm, 5 um	1 ea	23,210	27,619
505064	Discovery RP-Amide, 25 cm x 4.6 mm, 5 um	1 ea	25,000	29,749
567513-U	Discovery HS F5, 5 cm x 4.6 mm, 5 um	1 ea	16,070	19,123
567516-U	Discovery HS F5, 15 cm x 4.6 mm, 5 um	1 ea	23,210	27,619
567517-U	Discovery HS F5, 25 cm x 4.6 mm, 5 um	1 ea	25,000	29,749

Note: All prices in Indian Rupees. Taxes & other levies extra as applicable.

**Sigma Aldrich Chemicals Pvt. Ltd.**

#12, Bommasandra-Jigani Link Road, Bangalore - 560 100

T +91 80 6621 9600 F +91 80 6621 9650 E india@sial.com

New Delhi +91 11 4358 8000

Kolkata +91 33 4013 8000

Mumbai +91 22 2570 2364

Lucknow +91 522 400 3455

Chennai +91 44 4214 8991

Pune +91 20 2553 9079

Chandigarh +91 172 463 0255

Hyderabad +91 40 4015 5488

Ahmedabad +91 98250 62898

**SIGMA-ALDRICH**