

Cat#	Product	Pack Size	Duty Free Price
A9099	Acrylamide	1kg	6,590
A9539	Agarose, for routine use	100g	4,200
A9539	Agarose, for routine use	500g	11,088
A4718	Agarose, high resolution	100g	22,170
A9414	Agarose, low melting point	50g	11,880
M2022	Bis-acrylamide	250g	4,807
B6768	Boric Acid	1kg	1,393
C9426	CHAPS	5g	6,805
25666	Chloroform Isoamyl Alcohol Mixture 24:1	500ml	6,160
D5758	DEPC	100ml	8,675
D8418	Dimethyl sulfoxide	250ml	4,621
D8161	DTE	50g	18,510
D9779	DTT	25g	10,900
E5134	EDTA	500g	4,335
E7637	Ethidium bromide	5g	2,600
G5516	Glycerol	1l	1,607
G8790	Glycine	1kg	2,105
G3272	Guanidine hydrochloride	1kg	5,200
G9277	Guanidine thiocyanate	500g	7,680
H3784	HEPES Sodium Salt	500g	10,650
I5513	Immidazole	25g	8,670
I6758	IPTG	10g	11,260
M3148	2-Mercaptoethanol	250ml	1,852
P5413	PEG, Avg Mol Wt 8,000	2kg	4,364
P1037	Phenol	500g	4,287
P4557	Phenol, equilibrated with Tris Hcl & EDTA	400ml	3,322
P2069	Phenol Chloroform Isoamyl Alcohol 25:24:1	400ml	4,810
P2308	Proteinase K	100mg	6,320
R6513	Ribonuclease A	50mg	6,110
R0901	RNAlater	100ml	4,335
R0901	RNAlater	500ml	12,260
R2020	RNaseZAP	250ml	2,255
R2020	RNaseZAP	6x250ml	11,420
L4390	Sodium Dodecyl DS (Lauryl sulfate)	1kg	8,295
S0389	Sucrose	5kg	2,813
T7024	TEMED	100ml	2,230
T8787	Triton X 100	250ml	929
T6066	Trizma Base (Tris)	1kg	2,600
T6066	Trizma Base (Tris)	5kg	6,874
T5941	Trizma hydrochloride (Tris HCl)	1kg	4,269
U5378	Urea	1kg	2,230
U5378	Urea	5kg	5,880
W4502	Water (Molecular Biology)	1L	3,084
B9146	X-gal	500mg	5,075

Note: All prices in Indian Rupees. Taxes & other levies extra as applicable.

Sigma Aldrich Chemicals Pvt. Ltd.

#12, Bommasandra-Jigani Link Road, Bangalore - 560 100

T +91 80 6621 9600 F +91 80 6621 9650 E india@sial.com

New Delhi +91 11 4358 8000 Kolkata +91 33 4013 8000 Mumbai +91 22 4087 2364

Lucknow +91 522 400 3455 Chennai +91 44 4214 8991 Pune +91 20 2553 9079

Chandigarh +91 172 463 0255 Hyderabad +91 40 4015 5488 Ahmedabad +91 79 2754 1971

SIAL/LS/11/0410