

Cat#	Product	Pack Size	Duty Free Price	Duty Paid Price
NMR Reference Standards				
487104	NMR Std 0.1% Ethylbenzene/0.01% TMS/CDCl ₃ , 1H Sensitivity Std	1 pak	8,729	11,229
487163	NMR Std 1% Chloroform/Acetone-d ₆ , 1H Line Shape Std	1 pak	11,570	15,238
551368	NMR Std 40% p-Dioxane/Benzene-d ₆ , Cpw90, Sensitivity Standard	1 pak	8,425	10,838
612685	NMR Std 0.05% Trifluorotoluene/Benzene-d ₆ , 19F Sensitivity Std	1 pak	6,630	8,529
551392	NMR Std 0.0485M Triphenyl phosphate /CDCl ₃ , 31P Sensitivity Std	1 pak	14,810	19,051
LC-NMR Solvents				
530883	Acetonitrile-d ₃ , 99.8% atom % D	1 lit	149,500	192,316
563102	Acetonitrile-d ₃ , 99.8 atom % D, D ₂ O ~15-20 %	1 lit	113,000	145,362
530867	Deuterium oxide, 99.9 atom % D	1 lit	64,630	83,140
530875	Methanol - d ₄ , 99.8 atom %D	1 lit	236,900	304,746
NMR Solvents				
151823	Chloroform-d, Screw-cap bottle, Screw-cap bottle	100 g	780	1,003
225789	Chloroform-d, Screw-cap bottle, 0.03% v/v TMS, Screw-cap bottle	100 g	780	1,003
548537	Methyl-d ₃ alcohol-d, Septum Bottle	10 ml	1,620	2,084
548537	Methyl-d ₃ alcohol-d, Septum Bottle	50 ml	7,400	9,519
441384	Methyl-d ₃ alcohol-d, Ampule	10 x 0.75 ml	900	1,158
547239	Methyl Sulfoxide-d ₆ , Septum Bottle	10 ml	700	900
547239	Methyl Sulfoxide-d ₆ , Septum Bottle	50 ml	3,250	4,181
441392	Methyl Sulfoxide-d ₆ , Ampule	10 x 0.75 ml	780	1,003
151874	Methyl Sulfoxide-d ₆ , Ampule	10 g	700	900
296147	Methyl Sulfoxide-d ₆ , contains 0.03% v/v TMS, Ampule	10 g	3,250	1,029
151882	Deuterium Oxide	100 g	3,352	4,312
Wilmad NMR Tubes				
Z271993	Wilmad NMR Tubes for 300MHz Standard, 7 in length (507PP7) (1pk = 5)	1 pak	2,247	2,959
Z274461	Wilmad NMR Tubes for 300MHz Standard, 8 in length (507PP8) (1pk = 5)	1 pak	2,634	3,469
Z274275	Wilmad NMR Tubes for 400MHz Standard, 7 in length (527PP7) (1pk = 5)	1 pak	3,169	4,174
Z274526	Wilmad NMR Tubes for 400MHz Standard, 8 in length (527PP8) (1 pk = 5)	1 pak	3,514	4,628
Z272019	Wilmad NMR Tubes for 500MHz Standard, 7 in length (528PP7) (1 pk = 5)	1 pak	3,641	4,795
Z274291	Wilmad NMR Tubes for 500MHz Standard, 8 in length (528PP8) (1 pk = 5)	1 pak	4,102	5,402
Z272027	Wilmad NMR Tubes for 600MHz Standard, 7 in length (535PP7) (1 pk = 5)	1 pak	5,080	6,691
Aldrich NMR Tubes				
Z412805	Aldrich NMR Tubes for 300MHz Standard 7 in length (1PK=5)	1 pak	3,479	4,582
Z412813	Aldrich NMR Tubes for 300MHz Standard 8 in length (1PK=5)	1 pak	3,891	5,125
Z412848	Aldrich NMR Tubes for 400MHz Standard 7 in length (1PK=5)	1 pak	5,240	6,901
Z412856	Aldrich NMR Tubes for 400MHz Standard 8 in length (1PK=5)	1 pak	5,764	7,591
Z412864	Aldrich NMR Tubes for 500MHz Standard 7 in length (1PK=5)	1 pak	7,365	9,700
NMR Tube Cleaner				
Z422843	Five Position NMR Tube Cleaner System, 5 mm diameter	1 ea	26,520	34,928
Z513466	Five Position NMR Tube Cleaner System, 3 mm diameter	1 ea	27,600	36,350
NMR Tube Carriers / Racks				
Z286095	Unbreakable NMR Tube carrier fits into labcoat - Red	1 ea	517	681
Z286052	Unbreakable NMR Tube carrier fits into labcoat - White	1 ea	524	690
Z286109	Unbreakable NMR Tube carrier fits into labcoat - Blue	1 ea	524	690
Z286192	Unbreakable NMR Tube carrier fits into labcoat - Assortment pack of 3	1 ea	1,463	1,927
Z118257	Polyethylene NMR Tube Rack for 72 positions - 5mm tubes	1 ea	2,250	2,963
Z514314	Stainless steel NMR Tube Rack for 10 positions - 5 mm tubes	1 ea	3,700	4,873
Z514322	Stainless steel NMR Tube Rack for 20 positions - 5 mm tubes	1 ea	5,478	7,215

Note: All prices in Indian Rupees. Taxes & other levies extra as applicable.

Sigma Aldrich Chemicals Pvt. Ltd.

#12, Bommasandra-Jigani Link Road, Bangalore - 560 100

T +91 80 6621 9600 F +91 80 6621 9650 E india@sial.com

New Delhi +91 11 4358 8000

Kolkata +91 33 4013 8000

Mumbai +91 22 2570 2364

Lucknow +91 522 400 3455

Chennai +91 44 4214 8991

Pune +91 20 2553 9079

Chandigarh +91 172 463 0255

Hyderabad +91 40 4015 5488

Ahmedabad +91 98250 62898

SIGMA-ALDRICH®