

Cat#	Product	Sample Scale	Pack Size	Duty Free Price	Duty Paid Price
<b>Sample Preparation</b>					
<b>Protein Sample Preparation Kits</b>					
PROTMEM	ProteoPrep Membrane Extraction Kit	Min 6 (2ml)	1 Kit	11,910	15,686
PROTTWO	ProteoPrep Universal Extraction Kit	Min 10 (2ml)	1Kit	11,570	15,238
PROTTOT	ProteoPrep Total Extraction Sample Kit	Min 10 (2ml)	1Kit	15,540	20,467
PROTDT	ProteoPrep Detergent Sample Pack (10 detergents)	Varies with App	1Kit	17,460	22,995
<b>Protein Depletion Kits</b>					
PROTBA	ProteoPrep Blue Albumin and IgG Depletion Kit	25 samples	1Kit	18,820	24,787
PROTIA	ProteoPrep Immunoaffinity Albumin and IgG Depletion Kit	10 samples	1Kit	24,610	28,231
PROT20S	ProteoPrep 20 Plasma Immunodepletion Kit - 1 column	~100 runs/col	1Kit	72,600	95,617
PROT20	ProteoPrep 20 Plasma Immunodepletion Kit - 3 columns	~100 runs/col	1Kit	196,000	258,139
<b>Protein Enhancement Kits</b>					
PROTRA	ProteoPrep Reduction and Alkylation Kit	App Dependent	1Kit	3,680	4,847
<b>Organelle Enrichment and Analysis Kits</b>					
CPISO	Chloroplast Isolation Kit	Up to 18	1Kit	28,240	37,193
MITOISO1	Mitochondria Isolation Kit	10-20g Tissue	1Kit	29,940	39,432
MITOISO2	Mitochondria Isolation Kit (for Cells)	10-20g Tissue	1Kit	19,560	25,761
LYSISO1	Lysosome Isolation Kit	Up to 20g Tissue	1Kit	21,520	28,343
ER0100	Endoplasmic Reticulum Isolation Kit	Up to 50g Tissue	1Kit	19,390	25,537
CYTOCOX1	Cytochrome c Oxidase Assay Kit	100 Tests	1Kit	21,770	28,672
NUC101	Nuclei EZ Prep Kit	25 Preps	1Kit	10,340	13,618
NUC201	Nuclei PURE Prep Kit (For Pure & Fragile Nuclei)	15 Preps	1Kit	20,750	27,328
NXTRACT	CellLytic NuCLEAR Extraction Kit (For Nuclear Proteins)	App Dependent	1Kit	19,840	26,130
GL0010	Golgi Isolation Kit	50gm tissue	1 kit	19,020	25,050
PEROX1	Peroxisome Isolation Kit	50gm tissue	1 kit	22,380	29,475
CELLYTPN1	CellLytic PN Extraction Kit (For Plant Nuclear Proteins)	App Dependent	1Kit	20,070	26,432
<b>Cell Lysis &amp; Protein Extraction</b>					
B7435	CellLytic B (for Bacteria)	1-25g	50ml	2,802	3,690
CB0050	CellLytic B Plus (for Bacteria) with Lysozyme and Benzonase	5g	1 Kit	8,602	11,329
C5236	CellLytic IB (for Inclusion Bodies)		25ml	3,016	3,972
			100ml	9,658	12,720
B2978	CellLytic M (for Cultured Mammalian Cells)	App Dep	50ml	2,796	3,682
C3228	CellLytic MT (for Mammalian Tissues)		50ml	2,796	3,682
C2360	CellLytic P (for Plant Cells)		50ml	2,796	3,682
C4482	CellLytic Y (for Yeast)		50ml	2,588	3,408
C1990	CellLytic Express (for In-culture Bacterial Lysis)		25ml	1,814	2,389
CE0050	CellLytic MEM Protein Extraction Kit	80 Tests	1 Kit	12,850	16,924
<b>2D Electrophoresis</b>					
<b>IPG Strips</b>					
I2906	ProteoGel IPG Strips, 7 cm, pH 4-7	-	12 per pack	5,649	7,440
I7406	ProteoGel IPG Strips, 7 cm, pH 6-11	-	12 per pack	5,495	7,237
I3281	ProteoGel IPG Strips, 7 cm, pH 8-11	-	12 per pack	5,715	7,527
I3656	ProteoGel IPG Strips, 11 cm, pH 3-5	-	12 per pack	5,715	7,527
I3406	ProteoGel IPG Strips, 11 cm, pH 3-10	-	12 per pack	5,715	7,527
I3531	ProteoGel IPG Strips, 11 cm, pH 4-7	-	12 per pack	5,649	7,440
I3781	ProteoGel IPG Strips, 11 cm, pH 5-8	-	12 per pack	5,715	7,527
I7531	ProteoGel IPG Strips, 11 cm, pH 6-11	-	12 per pack	5,495	7,237
I3906	ProteoGel IPG Strips, 11 cm, pH 8-11	-	12 per pack	5,715	7,527
<b>Buffers</b>					
I7281	ProteoGel IPG Equilibration Buffer	-	50ml	7,073	9,315
T5196	ProteoGel Tris-Acetate Sample Buffer 5X Concentrate	-	10x1ml vials	1,914	2,521
T2821	ProteoGel Tris-Tricine-SDS Electrode Buffer (1 pk makes 5L)	-	10 packs	17,520	23,074
<b>Gel Staining</b>					
G1041	EZBlue Gel Staining Reagent	-	500ml	3,670	4,834
PROTSIL1	ProteoSilver	-	1 kit	10,720	14,119
PROTSIL2	ProteoSilver Plus (MALDI Compatible)	-	1 kit	13,490	17,767
S4942	SYPRO Ruby	-	1 kit	5,010	6,598
O3038	RuBP Stain	-	50ul	7,645	9,834

Note: All Prices in Indian Rupees. Taxes & other levies extra as applicable

Cat#	Product	Sample Scale	Pack Size	Duty Free Price	Duty Paid Price
<b>Mass Spectrometry</b>					
<b>Trypsin &amp; Proteases</b>					
T6567	Trypsin, Proteomics Grade		20ug	2,027	2,670
			5 x 20ug	4,485	5,907
T7575	Trypsin Singles, Proteomis Grade		96 x 1ug	7,895	10,398
TT0010	Trypsin Spin Columns, Proteomics Grade	10-100ug	10 columns	12,130	15,976
PP0100	Trypsin Profile In-Gel Digest Kit	100 spots	1 Kit	11,240	14,803
PP0500	Protease Profiler Kit	5,900ug	1 Kit	28,800	37,931
P3623	<sup>18</sup> O Proteome Profiler Kit	12 Expts	1 Kit	38,340	50,495
<b>Calibration Kits</b>					
MSCAL1	ProteoMass Peptide & Protein Kit (757 to 66,000 Daltons)	-	1 Kit	20,410	26,881
MSCAL2	ProteoMass Peptide Kit (757 to 3,500 Daltons)	-	1 Kit	20,410	26,881
MSCAL3	ProteoMass Protein Kit (5,700 to 66,000 Daltons)	-	1 Kit	20,410	26,881
MSCAL4	ProteoMass vMALDI Kit (5,700 to 66,000 Daltons)	-	1 Kit	19,400	25,550
<b>Guanidination Kit</b>					
MS0100	ProteoMass Guanidination Kit	96 Rxn	1 Kit	20,070	26,433
<b>MALDI Matrices</b>					
C8982	ProteoMass a-Cyano-4-Hydrocinnamic Acid	-	10x10mg	8,720	11,217
85429	Sinapic Acid (Sinipinic Acid)	-	1g	2,181	2,806
			5g	8,442	10,860
54793	2-(4-Hydroxyphenylazo) benzoic acid [HABA]	-	1g	1,409	1,813
			5g	5,435	6,992
85707	2,5-Dihydroxybenzoic Acid [DHB]	-	250mg	1,509	1,941
			1g	4,843	6,230
14078	Succinic Acid	-	1g	1,389	1,787
			5g	5,430	6,985
37468	2,6-Dihydroxyacetophenone [DHAP]	-	1g	1,940	2,496
			5g	7,540	9,699
46278	Ferrulic Acid	-	1g	1,668	2,146
			5g	6,160	7,924
60018	Caffeic Acid	-	1g	2,870	3,692
			5g	11,200	14,408
49771	Glycerol	-	5ml	3,482	4,479
<b>Protein Quantitation</b>					
BCA1	Bicinchoninic Acid Kit (for 200-1000 ug/ml protein)	~500 Assays	1 kit	13,950	18,373
QPBCA	QuantiPro BCA Assay Kit (for 0.5-30ug/ml protein)	App Dependent	1 kit	15,310	20,164
B6916	Bradford Reagent	-	500ml	3,215	4,234
F9252	Folin & Ciocalteu's Phenol Reagent	-	500ml	5,820	7,665
			1L	9,605	12,650
FP0010	FluoroProfile Protein Quantitation Kit	App Dependent	1 kit	14,360	18,913
<b>Protease Inhibitor Cocktails</b>					
P2714	Protease Inhibitor Cocktails for General Use, powder	-	1btl	2,552	3,361
P8465	Protease Inhibitor Cocktail for Bacterial Cells	5ml for 20g	5ml	3,011	3,966
			25ml	12,020	15,831
P8849	Protease Inhibitor Cocktail for Histidine Tagged Proteins	1ml for 20g	1ml	3,011	3,966
			5ml	12,020	15,831
P8340	Protease Inhibitor Cocktail for Mammalian Tissues	1ml for 20g	1ml	3,056	4,025
			5ml	12,130	15,976
P9599	Protease Inhibitor Cocktail for Plant Cells	1ml for 30g	1ml	2,983	3,929
			5ml	11,910	15,686
P8215	Protease Inhibitor Cocktail for Fungal and Yeast Cells	1ml for 20g	1ml	3,011	3,966
			5ml	12,020	15,831
P1860	Protease Inhibitor Cocktail for Tissue Culture Media	1:200 ratio	1ml	5,030	6,625
INHIB1	Protease Inhibitor Panel (14 components)	-	1 kit	17,240	22,706
P2850	Phosphatase Inhibitor Cocktail 1 For Acid & Alk Phosphatases and Tyrosine Protein Phosphatases	100 fold dil	1ml	3,024	3,983
			5ml	12,020	15,831
P5726	Phosphatase Inhibitor Cocktail 2 For L-isozymes of Alk Phosphatases and Ser/Thr Phosphatases	100 fold dil	1ml	3,086	4,064
			5ml	12,240	16,121

Note: All Prices in Indian Rupees. Taxes & other levies extra as applicable

**Sigma Aldrich Chemicals Pvt. Ltd.**

#12, Bommasandra-Jigani Link Road, Bangalore - 560 100

T +91 80 6621 9600 F +91 80 6621 9650 E india@sial.com

New Delhi +91 11 4358 8000 Kolkata +91 33 4013 8000

Mumbai +91 22 2570 2364

Lucknow +91 522 400 3455 Chennai +91 44 4214 8991

Pune +91 20 2553 9079

Chandigarh +91 172 463 0255 Hyderabad +91 40 4015 5488

Ahmedabad +91 98250 62898

**SIGMA-ALDRICH®**