

Ascentis Express HPLC Columns with Fused-Core Technology

Extreme Performance on Any LC System

- *Twice the Speed and Efficiency*
- *Extreme Performance on ANY LC System*
- *Half the Backpressure*
- *Super-Sensitivity*
- *Super-Ruggedness*



*Terms & Conditions:

- Offer valid till 31st October 2009
- For Singapore customers only
- Unless otherwise stated, promotion "Y25" is applicable to Selected Products as stated in this flyer
- Promotion Code "Y25" must be quoted at time of order to qualify for the offer.
- For phone inquiries, the promotion code must be quoted with the product numbers.
- For faxed and postal orders, the promotion code must be entered beside the product number for which the offer applies.
- For orders via the internet, the promotion code must be entered in the [Promo Code] box next to the product numbers.
- We regret we are unable to credit the offer value when the promotion code is not quoted at the time of the order.

Product Code	Description	Promotion Price! (S\$)	Usual Prices (S\$)
C8 Columns			
53839-U	ASCENTIS EXPRESS C8 2.7UM 3CM X 2.1MM	506.00	974.22
53831-U	ASCENTIS EXPRESS C8 2.7UM 5CM X 2.1MM	686.55	1265.07
53843-U	ASCENTIS EXPRESS C8 2.7UM 7.5CM X 2.1MM	759.00	1392.68
53832-U	ASCENTIS EXPRESS C8 2.7UM 10CM X 2.1MM	868.25	1581.45
53834-U	ASCENTIS EXPRESS C8 2.7UM 15CM X 2.1MM	1,005.10	1847.04
53844-U	ASCENTIS EXPRESS C8 2.7UM 3CM X 3.0MM	506.00	974.22
53848-U	ASCENTIS EXPRESS C8 2.7UM 5CM X 3.0MM	686.55	1265.07
53849-U	ASCENTIS EXPRESS C8 2.7UM 7.5CM X 3.0MM	759.00	1392.68
53852-U	ASCENTIS EXPRESS C8 2.7UM 10CM X 3.0MM	868.25	1581.45
53853-U	ASCENTIS EXPRESS C8 2.7UM 15CM X 3.0MM	1,005.10	1847.04
53857-U	ASCENTIS EXPRESS C8 2.7UM 3CM X 4.6MM	506.00	974.22
53836-U	ASCENTIS EXPRESS C8 2.7UM 5CM X 4.6MM	686.55	1265.07
53858-U	ASCENTIS EXPRESS C8 2.7UM 7.5CM X 4.6MM	759.00	1392.68
53837-U	ASCENTIS EXPRESS C8 2.7UM 10CM X 4.6MM	868.25	1581.45
53838-U	ASCENTIS EXPRESS C8 2.7UM 15CM X 4.6MM	1,005.10	1847.04

Enquiries? Contact us at:

Sigma-Aldrich Pte Ltd
 Tel: (65) 6779 1200
 Fax: (65) 6779 1822
 Email : sapl@sial.com
<http://www.sigma-aldrich.com/singapore>

For more information on Ascentis Express HPLC Columns, visit us at sigma-aldrich.com/express

• *Technology Leadership* • *Global Reach, Local Availability* • *Unrivalled Service*

Ascentis Express "Y25" Promotion* Up to > 50% Discount

*Terms & Conditions:

- Offer valid till 31st October 2009
- For Singapore customers only
- Unless otherwise stated, promotion "Y25" is applicable to Selected Products as stated in this flyer
- Promotion Code "Y25" must be quoted at time of order to qualify for the offer.
- For phone inquiries, the promotion code must be quoted with the product numbers.
- For faxed and postal orders, the promotion code must be entered beside the product number for which the offer applies.
- For orders via the internet, the promotion code must be entered in the [Promo Code] box next to the product numbers.
- We regret we are unable to credit the offer value when the promotion code is not quoted at the time of the order.

Enquiries? Contact us at:

Sigma-Aldrich Pte Ltd

Tel: (65) 6779 1200

Fax: (65) 6779 1822

Email : sapl@sial.com

<http://www.sigma-aldrich.com/singapore>

Product Code	Description	Promotion Price! (S\$)	Usual Prices (S\$)
C18 Columns			
53802-U	ASCENTIS EXPRESS C18 2.7UM 3CM X 2.1MM	506.00	1050.12
53822-U	ASCENTIS EXPRESS C18 2.7UM 5CM X 2.1MM	686.55	1265.07
53804-U	ASCENTIS EXPRESS C18 2.7UM 7.5CM X 2.1MM	759.00	1454.95
53823-U	ASCENTIS EXPRESS C18 2.7UM 10CM X 2.1MM	868.25	1581.45
53825-U	ASCENTIS EXPRESS C18 2.7UM 15CM X 2.1MM	1,005.10	1847.01
53805-U	ASCENTIS EXPRESS C18 2.7UM 3CM X 3.0MM	506.00	1050.12
53811-U	ASCENTIS EXPRESS C18 2.7UM 5CM X 3.0MM	686.55	1328.44
53812-U	ASCENTIS EXPRESS C18 2.7UM 7.5CM X 3.0MM	759.00	1454.95
53814-U	ASCENTIS EXPRESS C18 2.7UM 10CM X 3.0MM	868.25	1606.75
53816-U	ASCENTIS EXPRESS C18 2.7UM 15CM X 3.0MM	1,005.10	1847.01
53818-U	ASCENTIS EXPRESS C18 2.7UM 3CM X 4.6MM	506.00	974.22
53826-U	ASCENTIS EXPRESS C18 2.7UM 5CM X 4.6MM	686.55	1265.07
53819-U	ASCENTIS EXPRESS C18 2.7UM 7.5CM X 4.6MM	759.00	1392.68
53827-U	ASCENTIS EXPRESS C18 2.7UM 10CM X 4.6MM	868.25	1581.45
53829-U	ASCENTIS EXPRESS C18 2.7UM 15CM X 4.6MM	1,005.10	1847.01
53994-U	ASCENTIS EXPRESS C18 2.7UM 5X2.1 VAL PK&	2,168.90	3795.22
53995-U	ASCENTIS EXPRESS C18 2.7UM 10X4.6 VAL &	2,711.70	4744.15
53996-U	ASCENTIS EXPRESS C18 2.7UM 15X4.6 VAL &	3,167.10	5541.04
HILIC Columns			
53933-U	ASCENTIS EXPRESS HILIC 2.7UM 3CMX2.1	556.60	974.22
53934-U	ASCENTIS EXPRESS HILIC 2.7UM 5CMX2.1M	723.35	1265.07
53938-U	ASCENTIS EXPRESS HILIC 2.7UM 7.5CMX2.1M	795.80	1391.58
53939-U	ASCENTIS EXPRESS HILIC 2.7UM 10CMX2.1MM	903.90	1581.45
53946-U	ASCENTIS EXPRESS HILIC 2.7UM 15CMX2.1M	1,055.70	1847.01
53964-U	ASCENTIS EXPRESS HILIC 2.7UM 3CMX3.0MM	556.60	974.22
53967-U	ASCENTIS EXPRESS HILIC 2.7UM 5CMX3.0MM	723.35	1265.07
53969-U	ASCENTIS EXPRESS HILIC 2.7UM 7.5CMX3.0MM	795.80	1391.58
53970-U	ASCENTIS EXPRESS HILIC 2.7UM 10CMX3.0MM	903.90	1581.45
53972-U	ASCENTIS EXPRESS HILIC 2.7UM 15CMX3.0M	1,055.70	1848.12
53974-U	ASCENTIS EXPRESS HILIC 2.7UM 3CMX4.6M	556.60	974.22
53975-U	ASCENTIS EXPRESS HILIC 2.7UM 5CMX4.6MM	723.35	1265.07
53977-U	ASCENTIS EXPRESS HILIC 2.7UM 7.5CMX4.6MM	795.80	1391.58
53979-U	ASCENTIS EXPRESS HILIC 2.7UM 10CMX4.6MM	903.90	1581.45
53981-U	ASCENTIS EXPRESS HILIC 2.7UM 15CMX4.6MM	1,055.70	1847.01