

SIGMA-ALDRICH OCEAN-FREIGHT STOCKING LIST



PAY NO MORE[^] additional shipping charges for the ocean-freighted chemicals!
PLACE YOUR ORDER* now before they get swept off the shelves.
CONTACT US at sapl@sial.com for a quote today!

Item No.	Product No.	Description	Ex-stock as of 26 Sep 2011	Stock ETA Dec 2011
1	240656-100G	1,2-DIBROMOETHANE, 99+%	5	
2	157260-100G	1-HYDROXYBENZOTRIAZOLE HYDRATE	9	
3	01680-250ML	ACROLEIN, STAB.	4	5
4	240532-100ML	ALLYL ALCOHOL, 99+%	2	
5	23150-100ml	ALLYL CHLOROFORMATE, STAB.	17	
6	145831-250ML	ALLYLAMINE, 98%	11	
7	145831-1L	ALLYLAMINE, 98%	8	
8	419508-100G	BORON TRIBROMIDE, 99+%	4	10
9	277576-450G	BROMINE, 99.5+%, A.C.S. REAGENT	0	2
10	186171-100ML	BUTYLLITHIUM, 1.6M SOLUTION IN HEXANES	10	61
11	186171-1L	BUTYLLITHIUM, 1.6M SOLUTION IN HEXANES	9	
12	230707-100ML	BUTYLLITHIUM, 2.5M SOLUTION IN HEXANES	0	2
13	317276-250ML	CHLOROACETALDEHYDE SOLUTION	4	
14	167479-100G	CHLOROACETONE, 95%	0	5
15	100331-100G	CHLOROMETHYL METHYL ETHER, TECH.	11	
16	26388-100ML	CHLOROSULFONIC ACID	7	
17	60811-25G	COBALT CARBONYL, MOISTENED WITH HEXANE	24	
18	C91492-25G	CYANOGEN BROMIDE, 97%	0	3
19	C91492-100G	CYANOGEN BROMIDE, 97%	0	1
20	C105198-25G	CYCLOHEXYL ISOCYANATE	10	
21	11627-250ML-F	DIETHYL AZODICARBOXYLATE SOLUTION, ~40%	39	
22	133973-100G	ETHYL BROMOACETATE, 98%	0	5
23	185892-500G	ETHYL CHLOROFORMATE, 97%	8	
24	185922-500ML	FURAN, 99+%	14	
25	208450-100G	GERMANIUM(IV) CHLORIDE, 99.99%	2	
26	H1009-500ML	HYDROGEN PEROXIDE 30% (W/W) SOLUTION	2	
27	I8507-100ml	IODOMETHANE, 99%	0	7
28	195731-1kg	IRON(0)PENTACARBONYL	4	
29	195731-250G	IRON(0)PENTACARBONYL	3	
30	523216-100ML	METHACRYLOYL CHLORIDE, 97 %	4	5
31	527955-1L	METHANESULFONYL CHLORIDE, 99.7+% (CMS)	0	
32	112771-5G	METHYL ISOTHIOCYANATE	4	
33	269549-100ML	METHYL VINYL KETONE, 99%	9	
34	197343-100ML	METHYLLITHIUM, 1.6M SOLUTION IN DIETHYL ETHER	1	3
35	80910-1L	PIVALOYL CHLORIDE	11	
36	460923-25ML	PROPARGYL CHLOROFORMATE, 96%	3	
37	195596-100ML	SEC-BUTYLLITHIUM, 1.4M SOLUTION IN CYCLOHEXANE	1	5
38	186198-100ml	T-BUTYL LITHIUM, 1.7M IN PENTANE	0	10
39	218472-100G	TETRAMETHYL ORTHOSILICATE, 98%	8	
40	218472-500G	TETRAMETHYL ORTHOSILICATE, 98%	17	
41	115150-100G	THIOPHOSGENE, 97%	19	
42	175552-100G	TRICHLOROSILANE, 99%	2	3
43	T72605-100ML	TRIMETHYLACETYL CHLORIDE, 99%	2	
44	257222-100G	TRIMETHYLALUMINIUM	4	

[^] Chemicals with special handling requirements are subjected to review.

* Supply will be on first-come-first-serve basis. Delivery may take 3 - 6 months for non ex-stock items.