

Aldrich 価格改定品のご紹介

ボロン酸類やフッ素化試薬の大幅値下げに引き続き、その他の有機合成用試薬 約6400品目を値下げいたしました。

最新価格を是非Webサイト Aldrich.com/chemprod-jp でご覧ください。

製品名	CAS	製品番号	価格(¥)
Benzyl chloroformate, 95%	[501-53-1]	119938-5G	2,300
		119938-100G	4,800
1-Boc-4-piperidone, 98%	[79099-07-3]	461350-5G	6,800
		461350-25G	20,000
		461350-100G	62,000
Bromobenzene, 99%	[108-86-1]	B57702-100ML	1,600
		B57702-500ML	4,500
		B57702-2L	13,600
6-Bromo-1-indanone, 98%	[14548-39-1]	597147-1G	9,300
<i>tert</i> -Butyl(chloro)diphenylsilane, 98%	[58479-61-1]	195537-2G	2,100
		195537-10G	5,000
		195537-50G	16,000
γ -Butyrolactone, \geq 99%	[96-48-0]	B103608-25G	1,500
		B103608-500G	3,200
		B103608-2.5KG	7,800
1-Chloroethyl chloroformate, 98%	[50893-53-3]	301485-5G	7,400
		301485-25G	20,200
Chlorosulfonyl isocyanate, 98%	[1189-71-5]	142662-25G	5,400
		142662-100G	16,200
		142662-1KG	93,000
Chlorotrimethylsilane, purified by redistillation, \geq 99% (TMCS)	[75-77-4]	386529-100ML	5,600
		386529-1L	34,000
1, 8-Diazabicyclo[5.4.0]undec-7-ene, 98% (DBU)	[6674-22-2]	139009-25G	2,200
		139009-100G	7,600
		139009-500G	17,200
Diethyl 1, 4-dihydro-2, 6-dimethyl-3, 5-pyridinedicarboxylate, 95%	[1149-23-1]	120227-1G	6,100
3, 4-Dihydro-2 <i>H</i> -pyran, 97%	[110-87-2]	D106208-100ML	2,500
		D106208-500ML	10,000
<i>N,N'</i> -Diisopropylcarbodiimide, 99% (DIC)	[693-13-0]	D125407-5G	1,700
		D125407-25G	4,700
		D125407-100G	17,100
3', 5'-Dimethoxy-4'-hydroxyacetophenone, 97%	[2478-38-8]	D134406-1G	3,400
		D134406-5G	11,500
		D134406-25G	40,000
2-Dimethylaminoethanol, \geq 98.0%	[108-01-0]	38990-250ML	1,900
		38990-1L	4,300
2, 2-Dimethylbutane, \geq 99.0%	[75-83-2]	39740-100ML	7,700
		39740-500ML	18,000
1, 3-Dimethyl-2-imidazolidinone, \geq 99.0% (DMEU, DMI)	[80-73-9]	40727-100ML	3,900
		40727-1L	26,900
(±)-6-Hydroxy-2, 5, 7, 8-tetramethylchromane-2-carboxylic acid, 97% (Trolox)	[53188-07-1]	238813-1G	9,200
		238813-5G	28,800
4-Iodobenzaldehyde, 96%	[15164-44-0]	263826-1G	11,000
2-Mercaptoethanol, \geq 99.0%	[60-24-2]	M6250-100ML	2,500
		M6250-250ML	4,000
		M6250-500ML	6,200
		M6250-1L	10,400
2-Methyl-2-butene, \geq 95.0%	[513-35-9]	86262-50ML-F	3,800
		86262-250ML-F	13,000
		86262-1L-F	40,900

製品名	CAS	製品番号	価格(¥)
1-Methylimidazole, 99%	[616-47-7]	M50834-100G	4,100
		M50834-500G	12,800
Methyl trifluoromethanesulfonate, 98%	[333-27-7]	164283-10G	10,500
		164283-50G	38,000
2-Octanone, 98%	[111-13-7]	O4709-25G	4,000
		O4709-500G	5,800
		O4709-2KG	8,300
O-(2, 3, 4, 5, 6-Pentafluorobenzyl)hydroxylamine hydrochloride, \geq 98% (PFBHA·HCl)	[57981-02-9]	194484-250MG	4,800
		194484-1G	14,000
1, 2, 2, 6, 6-Pentamethylpiperidine, 97% (PMP)	[79-55-0]	274631-5G	7,300
2-Phenylpyridine, 98%	[1008-89-5]	P33402-10G	11,200
		P33402-50G	33,000
Phosphorus(V) oxybromide, >95%	[7789-59-5]	376949-25G	14,000
Propionic anhydride, \geq 99%	[123-62-6]	240311-50G	2,700
Pyrrole, 98%	[109-97-7]	131709-25ML	3,300
		131709-100ML	8,200
		131709-500ML	28,000
2-Pyrrolidinone, 99%	[616-45-5]	P74370-25G	3,100
		P74370-500G	3,600
		P74370-1KG	4,200
Sodium dodecylbenzenesulfonate	[25155-30-0]	289957-25G	4,000
		289957-500G	5,600
		289957-1KG	10,500
1H-1, 2, 3-Triazole, 97%	[288-36-8]	333662-1G	4,500
		333662-5G	14,100
2, 2, 2-Tribromoethanol, 97%	[75-80-9]	T48402-5G	2,700
		T48402-25G	8,800
		T48402-100G	26,700
Trifluoromethanesulfonic acid, 98% (Triflic acid)	[1493-13-6]	158534-10G	2,800
		158534-50G	8,700
		158834-100G	13,400
Triphenylphosphine, 99%	[603-35-0]	T84409-1G	1,700
		T84409-25G	2,100
		T84409-100G	3,700
		T84409-500G	9,600
		T84409-1KG	14,400
Undecane, \geq 99%	[1120-21-4]	U407-25ML	2,600
		U407-100ML	4,100
Vinyl acetate, \geq 99%	[108-05-4]	V1503-25ML	2,000
		V1503-1L	4,300
		V1503-2L	6,000

この他にも多数の製品を値下げしております。最新価格は Aldrich.com/chemprod-jp でご確認ください。

©2011 Sigma-Aldrich Co. LLC. All rights reserved. SIGMA, SAFC, SIGMA-ALDRICH, ALDRICH, and SUPELCO are trademarks of Sigma-Aldrich Co. LLC, registered in the US and other countries. FLUKA is a trademark of Sigma-Aldrich GmbH, registered in the US and other countries. SAFC brand products are sold through Sigma-Aldrich, Inc. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see product information on the Sigma-Aldrich website at sigma-aldrich.com

- ・本カタログに掲載の製品及び情報は2011年11月1日現在の内容であり、掲載の品目、製品情報、価格等は予告なく変更される場合がございます。
- ・最新の情報は、弊社Webサイト(sigma-aldrich.com/japan)をご覧ください。
- ・掲載価格は希望納入価格(税別)です。詳細は販売代理店様へご確認ください。
- ・弊社の試薬は試験研究用のみを目的として販売しております。医薬品原料並びに工業用原料等としてご購入の際は、弊社ファインケミカル事業部までお問い合わせをお願いします。

SIGMA-ALDRICH®

シグマ アルドリッチ ジャパン株式会社

アナリティカル&ケミストリー事業部

〒140-0002 東京都品川区東品川2-2-24 天王洲セントラルタワー4F

製品に関するお問い合わせは、弊社テクニカルサポートへ

TEL:03-5796-7330 FAX:03-5796-7335 E-mail:sialjpts@sial.com

在庫照会・ご注文方法に関するお問い合わせは、弊社カスタマーサービスへ

TEL:03-5796-7320 FAX:03-5796-7325 E-mail:sialjpcs@sial.com

<http://www.sigma-aldrich.com/japan>