

Sigma-Aldrich Catalog Number	PCR Plate Product Description
D9064	Corning DNA-BIND™ Surface Multiwell plates 96 well, flat bottom
D9189	Corning DNA-BIND™ Surface Multiwell plates 8 well strip plate 12 per frame, flat bottom
C2356	Corning Microcentrifuge Tubes Cap Strip for 8 tubes 12 strips
P8981	FlexPlate™ 96 Well Plate, Natural
P4366	GeNunc Tube Tray and Holder Tube Tray and Holder
P2237	Greiner PCR Multiwell plates polycarbonate Type 1 for Biometra and Ericomp, 96 well
P2362	Greiner PCR Multiwell plates polycarbonate Type 2 for Hybaid, 96 well
P2487	Greiner PCR Multiwell plates polycarbonate Type 3 for MJ, Coy, and Stratagene, 96 well
P2612	Greiner PCR Multiwell plates polycarbonate Type 4 for Perkin-Elmer and Thermolyne, 96-well
P2737	Greiner PCR Multiwell plates polycarbonate Type 5 for Techne, 96 well
P2862	Greiner PCR Multiwell plates polycarbonate Type 6 for Techne, 25 well
L3161	Greiner PCR Multiwell plates polycarbonate Lid for Types 1, 2, 3 and 4
L3286	Greiner PCR Multiwell plates polycarbonate Lid for Type 5
P1987	Greiner PCR Multiwell plates polypropylene 96 well, no skirt
P2112	Greiner PCR Multiwell plates polypropylene 384 well, fullskirt
Z37,191-2	Multiwell Plate for PCR polycarbonate, No
P4491	Nunc™ Amplification Plates 96 well without skirt
P4616	Nunc™ Amplification Plates 96 well with skirt
P4741	Nunc™ Amplification Plates 96 well with mini skirt
S6315	Nunc™ Amplification Plates 96 well Silicon spacer plate
P4866	Nunc™ Amplification Plates 384 well, white
P4991	Nunc™ Amplification Plates 384 well, black
P5116	Nunc™ Amplification Plates 384 well, natural
O0764	Nunc™ OmniTray non-treated with lid
O0639	Nunc™ OmniTray Maxisorp™ with lid
Z37,491-1	PCR multiwell plates 384-well
Z37,081-9	Replicator, 96-well Autoclavable
P3606	Thermowell® PCR Plate 96 well, natural
P3731	Thermowell® PCR Plate 96 well, black
P4106	Thermowell® PCR Plate 96 well, blue
P3981	Thermowell® PCR Plate 96 well, green
P4231	Thermowell® PCR Plate 96 well, red
P3856	Thermowell® PCR Plate 96 well, yellow
P4606	Thermowell® PCR Plate 384 well, natural
Z70,944-1	Thermowell® PCR Plate 384 well, polypropylene
P5231	Thermowell® PCR Plate black, polypropylene
P4856	Thermowell® PCR Plate blue, polypropylene
P4981	Thermowell® PCR Plate green, polypropylene
P4731	Thermowell® PCR Plate polypropylene, Red
P5106	Thermowell® PCR Plate yellow, polypropylene
T7817	UV Plate, 96 well, flat bottom PCR tube Domed cap for PCR
T9692	UV Plate, 96 well, flat bottom Strip tube no cap
C0981	UV Plate, 96 well, flat bottom Domed Cap Strip
C1106	UV Plate, 96 well, flat bottom Flat Cap Strip
T7942	UV Plate, 96 well, flat bottom PCR tube Domed cap
P6861	UV Plate, 96 well, flat bottom Rigid PCR plate 96 well, low profile
F2551	UV Plate, 96 well, flat bottom Adhesive PCR foil
U9632	UV Plate, 96 well, flat bottom To be determined
F2551	UV Plate, 96 well, flat bottom Adhesive PCR foil