

Product No	Size	Product Name	List Price	Special Price	Price/unit
D9307	50UN	JUMPSTART TAQ	728	154.44	3.09
	250UN	JUMPSTART TAQ	2886	579.15	2.32
	1.5KU	JUMPSTART TAQ	14625	1467.18	0.98
D4184	50UN	JUMPSTART TAQ WITHOUT Mg2+	652	154.44	3.09
	250UN	JUMPSTART TAQ WITHOUT Mg2+	2886	579.15	2.32
	1.5KU	JUMPSTART TAQ WITHOUT Mg2+	14625	1467.18	0.98
P2893	100RXN	JUMPSTART TAQ READYMIX	1898	604.89	
	400RXN	JUMPSTART TAQ READYMIX	6721	1595.88	
D5809	125UN	JUMPSTART ACCUTAQ LA DNA POLYMERASE	1853	630.63	5.05
	500UN	JUMPSTART ACCUTAQ LA DNA POLYMERASE	7163	2007.72	4.02
	1500UN	JUMPSTART ACCUTAQ LA DNA POLYMERASE	20800	4504.5	3
D7295	0.2ML	dNTP Mix (Solution of all four dNTPs)0.2 ml (2 µmo	450	38.61	
	0.5ML	dNTP Mix (Solution of all four dNTPs) 0.5 ml (5 µmo	939	90.09	
	20X0.2ML	dNTP Mix (Solution of all four dNTPs)0.2 ml (2 µmo	6656	746.46	