

Sigma-Aldrich 部分产品 半价促销!

促销代号: SAEX08001

注意事项: 以下产品促销价仅限于表中所列批号, 如需定购上述产品, 请务必将产品的批号告知我们的客服, 谢谢!

友情提醒: 鉴于以上产品的有效期较短, 请您在订购时谨慎选择。该系列产品一旦出仓, 恕不接受处理投诉及退货事宜。

Sigma-Aldrich公司保留此项活动的最终解释权。

英文品名	中文品名	货号	规格	原价 (RMB)	促销价(RMB)	品牌	批次	有效期
1-IODO-3-NITROBENZENE, 99%	1-碘-3-硝基苯, 99%	144495-25G	25g	398.97	199.49	ALDRICH	S11086-207	04/28/2008
BORANE-PYRIDINE COMPLEX, 8 M BH3	硼烷-吡啶络合物	179752-100G	100g	2265.12	1132.56	ALDRICH	S42433-227	06/05/2008
4-PHENYLAZOANILINE, 98%	对氨基偶氮苯, 98%	186368-25G	25g	283.14	141.57	ALDRICH	S11494-217	05/08/2008
5,5-DIMETHYL-1-PYRROLINE N-OXIDE, 97%	5,5-二甲基-1-吡咯啉氮氧化物, 97%	194581-1G	1g	2882.88	1441.44	ALDRICH	03221HA086	06/01/2008
sodium bis(2-methoxyethoxy)aluminum hydride solution, ≥65 wt. % in toluene	二(2-甲氧乙氧基)氢化铝钠溶液, ≥65 wt. % 于甲苯中	196193-50G	50g	424.71	212.36	ALDRICH	S42575-247	06/14/2008
DIISOBUTYLALUMINUM HYDRIDE, 1.0 M in tetrahydrofuran	二异丁基氢化铝, 1.0M 于四氢呋喃中	214981-800ML	800ml	2522.52	1261.26	ALDRICH	S39986-027	05/19/2008
CHROMIUM(III) CHLORIDE HEXAHYDRATE, 96%	六水合三氯化铬 (III), 96%	230723-100G	100g	270.27	135.14	ALDRICH	S18029-384	06/04/2008
POTASSIUM BIS(TRIMETHYLSILYL)AMIDE, 0.5M in toluene	双(三甲基硅烷基)氨基钾, 0.5M于甲苯中	277304-100ML	100ml	720.72	360.36	ALDRICH	S42585-257	06/20/2008
DIETHYLZINC, 1.0M SOLUTION IN HEXANES	二乙基锌溶液, 1M于正己烷中	296112-100ML	100ml	1029.6	514.80	ALDRICH	S42003-187	05/11/2008
Bromine (bromide-bromate) volumetric standard solution, 0.1 N in H2O,	溴滴定标准溶液, 0.1N于水中,	318698-500ML	500ml	244.53	122.27	ALDRICH	09124HD	06/24/2008
ETHYLENE GLYCOL, ANHYDROUS, 99.8%	无水乙二醇, 99.8%	324558-100ML	100ml	386.1	193.05	ALDRICH	08533HE247	06/19/2008
ETHYLENE GLYCOL, ANHYDROUS, 99.8%	无水乙二醇, 99.8%	324558-1L	1l	759.33	379.67	ALDRICH	08533HE247	06/21/2008
ETHYLMAGNESIUM BROMIDE solution, 1.0 M in tetrahydrofuran	溴化乙基镁溶液, 1.0M于四氢呋喃中	364673-100ML	100ml	540.54	270.27	ALDRICH	S42040-207	05/23/2008
TETRAHYDROFURAN ANHYDROUS, 99.9%, inhibitor free	无水四氢呋喃, 99.9%, 不含抑制剂	401757-2L	2l	1402.83	701.42	ALDRICH	09571TE177	04/28/2008
1,3-CYCLOHEXADIENE, 97%	1,3-环己二烯, 97%	C100005-100ML	100ml	7927.92	3963.96	ALDRICH	S35362-176	06/05/2008

ETHYL CYANOFORMATE, 99%	氰甲酯乙酯, 99%	E18859-10G	10g	592.02	296.01	ALDRICH	S34336-127	05/02/2008
ETHYL TRIFLUOROACETATE, 99%	三氟乙酸乙酯, 99%	E50000-100G	100g	978.12	489.06	ALDRICH	19119TA415	04/26/2008
2-PHENOXYETHANOL, PH EUR	2-苯氧基乙醇	10832-500ML	500ml	1068.21	534.11	FLUKA	20306P01	06/01/2008
BORANE DIMETHYLAMINE COMPLEX, purum, $\geq 97.0\%$ (RT)	硼烷-二甲胺络合物, $\geq 97.0\%$ (RT)	15584-25G	25g	836.55	418.28	FLUKA	22107B01	05/23/2008
2,3-DIMETHYLPENTANE, puriss. p.a., standard for GC, $\geq 99.0\%$ (GC)	2,3-二甲基戊烷, GC标准品, $\geq 99.0\%$	41085-5ML	5ml	1505.79	752.90	FLUKA	44905268	05/22/2008
ETHYNYLMAGNESIUM BROMIDE SOLUTION, puriss. p.a., standard for GC, $\geq 99.0\%$ (GC)	乙炔基溴化镁, GC标准品, $\geq 99.0\%$	46045-500ML	500ml	1338.48	669.24	FLUKA	11507B04	04/26/2008
HYDROXYLAMINE SOLUTION, purum, $\sim 50\%$ in H ₂ O (RT)	羟胺溶液, $\sim 50\%$ 浓度于水中 (RT)	55458-250ML	250ml	746.46	373.23	FLUKA	42407B11	05/28/2008
POLYSORBAT 80, PH EUR	聚山梨酯80	59924-100G-F	100g	231.66	115.83	FLUKA	54806P45	06/01/2008
SODIUM BOROHYDRIDE, purum p.a., $\geq 96\%$ (gas-volumetric)	硼氢化钠, $\geq 96\%$	71320-100G	100g	1003.86	501.93	FLUKA	22107B02	05/25/2008
TRIFLUOROACETIC ACID, BioChemika, for protein sequence analysis, $\geq 99.5\%$ (T)	三氟乙酸, BioChemika, 用于蛋白序列分析, $\geq 99.5\%$ (T)	73645-50ML-F	50ml	1003.86	501.93	FLUKA	11707359	05/28/2008
TRIFLUOROACETIC ACID, BioChemika, for protein sequence analysis, $\geq 99.5\%$ (T)	三氟乙酸, BioChemika, 用于蛋白序列分析, $\geq 99.5\%$ (T)	73645-50ML-F	50ml	1003.86	501.93	FLUKA	30307221	05/28/2008
Triethylammonium bicarbonate buffer, BioChemika, volatile buffer, ~ 1.0 M in H ₂ O	三乙胺重碳酸盐缓冲液, 挥发性, 1.0M于水中	90360-100ML	100ml	900.9	450.45	FLUKA	40806176	05/28/2008
P-XYLENE, puriss. p.a., standard for GC, $\geq 99.5\%$ (GC)	对二甲苯, GC标准品, $\geq 99.5\%$	95680-10ML	10ml	926.64	463.32	FLUKA	41506182	06/14/2008
BENZYL ALCOHOL, puriss., meets analytical specification of Ph. Eur., BP, NF, 99-100.5% (GC)	苯甲醇, 分析纯 Ph. Eur., BP, NF, 99-100.5% (GC)	24122-1L	1l	669.24	334.62	RIEDEL	71270	05/01/2008
Potassium hydroxide standard solution, solution (volumetric), 0.5 M in denatured ethanol with toluene	氢氧化钾标准溶液, 0.5M于含甲苯的变性乙醇中	35115-1L	1l	707.85	353.93	RIEDEL	72690	05/23/2008
Potassium hydroxide standard solution, solution (volumetric), 0.1 M in denatured ethanol with toluene	氢氧化钾标准溶液, 0.1M于含甲苯的变性乙醇中	35127-1L	1l	566.28	283.14	RIEDEL	72480	05/02/2008
standard	噻霉胺, 分析标准品	46039-250MG-R	250mg	1016.73	508.37	RIEDEL	2158X	06/07/2008

4-AMINOAZOBENZENE, OEKANAL®, analytical standard	4-氨基偶氮苯, 分析标准品	46130-250MG-R	250mg	398.97	199.49	RIEDEL	2170X	06/18/2008
SODIUM HYPOCHLORITE, SOLUTION, reagent grade, available chlorine ≥4 %	次氯酸钠溶液, 有效氯浓度 ≥4 %	239305-500ML	500ml	643.5	321.75	SIAL	17850	05/31/2008
Sodium borohydride, powder, reagent grade, ≥98.5%	硼氢化钠, 粉末, ≥98.5%	452882-100G	100g	797.94	398.97	SIAL	S41813-217	05/29/2008
L-Cysteine hydrochloride monohydrate	L-半胱氨酸盐酸盐一水合物	C6852-100G	100g	1003.86	501.93	SIAL	125K0368	04/30/2008
kanamyceticus, meets USP testing	卡那霉素, 符合 USP 标准, 粉末	K1637-1G	1g	501.93	250.97	SIAL	125K1247	06/20/2008
METHOTREXATE, meets USP testing specifications	甲氨蝶呤, USP标准	M9929-100MG	100mg	2136.42	1068.21	SIAL	076K1753	05/01/2008
Novobiocin sodium, meets USP testing specifications	新生霉素钠, USP标准	N6160-5G	5g	2175.03	1087.52	SIAL	045K10181	05/04/2008
L-CYSTEINE, ≥98%, from non-animal source, cell culture tested	L-半胱氨酸, ≥98%	C7352-10MG	10mg	193.05	96.53	SIGMA	037K0185	06/12/2008
GENTAMICIN SOLUTION, 10 mg/mL in deionized water, liquid, sterile-filtered, cell culture tested	庆大霉素溶液, 10mg/mL 于去离子水中, 无菌过滤, 细胞培养测试	G1272-10ML	10ml	154.44	77.22	SIGMA	057K2315	05/31/2008
from non-animal source, EP, JP, USP, suitable for manufacturing use, suitable for cell culture	甘氨酸, ≥98.5%, 非动物来源, EP, JP, USP标准, 适合生产用和细胞培养	G5417-1KG	1kg	2033.46	1016.73	SIGMA	066K8301	04/30/2008
L-GLUTAMINE-PENICILLIN-STREPTOMYCIN solution, stablized, sterile-filtered, cell culture tested	L-谷氨酰胺-青霉素-链霉素溶液, 无菌过滤, 细胞培养	G6784-100ML	100ml	849.42	424.71	SIGMA	056K2430	05/31/2008
HEMATOXYLIN SOLUTION, HARRIS MODIFIED	苏木精染液	HHS128-4L	4l	1570.14	785.07	SIGMA	116K4356	05/31/2008
MINIMUM ESSENTIAL MEDIUM EAGLE, With Earle's salts, L-glutamine, and non-essential amino acids, without sodium bicarbonate, powder, cell culture tested	MEM 培养基, Earle's 盐, L-谷胱氨酸, 非必需氨基酸, 无重碳酸钠, 粉末, 细胞培养用	M0643-10X1L	10X1L	514.8	257.40	SIGMA	055K8302	05/31/2008
MINIMUM ESSENTIAL MEDIUM EAGLE, AutoMod™, with Earle's salts, without L-glutamine and sodium bicarbonate, powder, cell culture tested	MEM 培养基, AutoMod™, Earle's 盐, 无L-谷胱氨酸和重碳酸钠, 粉末, 细胞培养用	M0769-10X1L	10X1L	501.93	250.97	SIGMA	055K8312	05/31/2008
MEDIUM 199, With Earle's salts, L-glutamine and sodium bicarbonate, liquid, sterile-filtered, cell culture tested	M199, Earle's 盐, L-谷胱氨酸和重碳酸钠, 液体, 无菌过滤, 细胞培养用	M4530-100ML	100ml	115.83	57.92	SIGMA	047K2416	04/30/2008

M2 MEDIUM With HEPES, without penicillin and streptomycin, liquid, sterile-filtered, mouse embryo tested	M2培养基, 含HEPES, 无青链霉素, 液体, 无菌过滤, 小鼠胚胎测试	M7167-50ML	50ml	270.27	135.14	SIGMA	057K2373	05/31/2008
M16 MEDIUM With sodium bicarbonate and lactic acid, without penicillin and streptomycin., liquid, sterile-filtered, mouse embryo tested	M16培养基, 含重碳酸钠和乳酸, 无青链霉素, 液体, 无菌过滤, 小鼠胚胎测试	M7292-100ML	100ml	373.23	186.62	SIGMA	057K2431	05/31/2008
M16 MEDIUM With sodium bicarbonate and lactic acid, without penicillin and streptomycin., liquid, sterile-filtered, mouse embryo tested	M16培养基, 含重碳酸钠和乳酸, 无青链霉素, 液体, 无菌过滤, 小鼠胚胎测试	M7292-50ML	50ml	218.79	109.40	SIGMA	057K2431	05/31/2008
PENICILLIN-STREPTOMYCIN SOLUTION, 100 ×, liquid, sterile-filtered, cell culture tested	青霉素-链霉素溶液, 100 ×, 液体, 无菌过滤, 细胞培养用	P0781-20ML	20ml	128.7	64.35	SIGMA	106K2320	04/30/2008
Penicillin - Streptomycin - Neomycin Solution (100x) Stabilized, liquid, sterile-filtered, cell culture tested	青霉素-链霉素-新霉素溶液, 100 ×, 液体, 无菌过滤, 细胞培养用	P4083-20ML	20ml	193.05	96.53	SIGMA	056K2434	05/31/2008
TC-100 INSECT MEDIUM With L-glutamine and sodium bicarbonate, liquid, sterile-filtered, insect cell culture tested	TC-100昆虫培养基, 含L-谷胱氨酸和重碳酸盐, 液体, 无菌过滤, 昆虫细胞培养用	T3160-1L	1L	797.94	398.97	SIGMA	057K2352	05/31/2008
Trypsin inhibitor from Glycine max (soybean) 1 ×, solution, sterile-filtered, cell culture tested	胰蛋白酶抑制剂, 1 ×溶液, 无菌过滤, 细胞培养用	T6414-100ML	100ml	836.55	418.28	SIGMA	116K0722	05/01/2008
WRIGHT-GIEMSA STAIN, MODIFIED	瑞氏-吉姆萨染料	WG16-500ML	500ml	617.76	308.88	SIGMA	106K4343	04/30/2008
m-Tolualdehyde-2,4-DNPH solution, 100 μg/mL in acetonitrile, ampule of 1 mL	m-甲苯甲醛-2,4-二硝基苯腙溶液, 100 μg/mL于乙腈中, 1ml安瓿瓶包装	47183		266.76	133.38	SUPELCO	LB29685	05/01/2008
Isobutyraldehyde-2,4-DNPH solution, 100 μg/mL in acetonitrile, ampule of 1 mL	异丁醛-2,4-二硝基苯腙溶液, 100 μg/mL于乙腈中, 1ml安瓿瓶包装	47886		266.76	133.38	SUPELCO	LB31462	05/01/2008
LpDNPH Cartridge, S10x, pkg of 10	LpDNPH 小柱, S10x, pkg of 10	505293		1488.24	744.12	SUPELCO	SP8802	05/01/2008