

Antibiotici

Terreni

Offerta speciale Prodotti per Colture Cellulari

Plastica

Codice promozionale da indicare sull'ordine: T19

Supplementi

Terreni

Codice Prodotto	Descrizione	Prezzo Speciale Euro
D1408-6X500ML	Dulbecco's Phosphate Buffered Saline (10X), without CaCl ₂ and MgCl ₂	20.00
D5671-6x500ML	Dulbecco's Modified Eagle's Medium (DMEM) With 4.5 g/L Glucose, Sodium Bicarbonate w/o L-glutamine	20.00
D5546-6x500ML	Dulbecco's Modified Eagle's Medium (1X) Liquid, with 1000 mg/L Glucose and Sodium Bicarbonate	20.00
D5796-6x500ML	Dulbecco's Modified Eagle's Medium (DMEM) With 4.5 g/L Glucose, Sodium Bicarbonate, L-glutamine w/o Sodium pyruvate	20.00
D6046-6x500ML	Dulbecco's Modified Eagle's Medium (DMEM) With 1 g/L Glucose, Sodium Bicarbonate, L-glutamine, Sodium pyruvate	20.00
D6171-6x500ML	Dulbecco's Modified Eagle's Medium (1X) Liquid, HEPES modification	20.00
D6421-6x500ML	DME/F-12 (1:1 Mixture) (1X) Liquid, w/o L-Glutamine, with 15mM HEPES	20.00
D6429-6x500ML	Dulbecco's Modified Eagle's Medium (DMEM) With 4.5 g/L Glucose, Sodium Bicarbonate, L-glutamine, Sodium pyruvate	20.00
D6546-6x500ML	Dulbecco's Modified Eagle's Medium (1X) Liquid, w/o L-Glutamine, with 4500 mg/L glucose, with 110 mg/L Sodium Pyruvate	20.00
D8537-6x500ML	Dulbecco's Phosphate Buffered Saline (DPBS) (1x) w/o calcium and magnesium	20.00
D8662-6x500ML	Dulbecco's Phosphate Buffered Saline (1x) With Calcium and magnesium	20.00
H9394-6x500ML	Hanks' Balanced Salt Solution (HBSS), with sodium bicarbonate w/o calcium and magnesium	20.00
I3390-6x500ML	Iscove's modified Dulbecco's medium (IMDM) with sodium bicarbonate w/o L-glutamine	20.00
L5520-6x500ML	L-15 Medium Leibowitz	20.00
M2154-6x500ML	Medium 199, with Earle's Salts	20.00
M2279-6x500ML	Minimum Essential Medium Eagle (MEM) With Earle's Salts and sodium bicarbonate w/o L-glutamine	20.00
M4655-6x500ML	Minimum Essential Medium Eagle (MEM) with Earle's salts, L-glutamine and sodium bicarb.	20.00
M5650-6x500ML	Minimum Essential Medium Eagle (1X), Liquid, with Earle's salts and aminoacids	20.00
N4888-6x500ML	Nutrient Mixture F-12 Ham (1x) with sodium bicarbonate w/o L-glutamine	20.00
R0883-6x500ML	RPMI-1640 Medium (1x) With Sodium Bicarbonate, w/o L-Glutamine	20.00
R5886-6x500ML	RPMI-1640 (1X) Liquid, w/o L-Glutamine, with 25mM HEPES	20.00
R8758-6x500ML	RPMI-1640 Medium with L-Glutamine, sodium bicarbonate	20.00

Supplementi

Codice Prodotto	Descrizione	Prezzo Speciale Euro
D2650-100ML	Dimethyl Sulfoxide Hybri-Max	100.00
D2650-5X10ML	Dimethyl Sulfoxide Hybri-Max	65.00
E8008-100ML	EDTA 0.02% Solution	7.50
S8636-100ML	Sodium Pyruvate solution 100mM	7.00
S8761-100ML	Sodium Bicarbonate solution	6.00
G7513-100ML	L-Glutamine 200 mM, Sterile filtered	11.00
G7513-20ML	L-Glutamine 200 mM, Sterile filtered	5.00
H0887-100ML	Hepes Buffer solution 1M	44.00
H8889-100ML	HISTOPAQUE-1077 HYBRI-MAX	28.00
H8889-500ML	HISTOPAQUE-1077 HYBRI-MAX	95.00
I3146-5ML	ITS Liquid Media Supplement (100X)	19.50
M7145-100ML	MEM Non-essential amino Acid Solution (100x)	9.00
T8154-100ML	Trypan Blue Solution	9.00

Validità offerta: 31 gennaio 2005

Antibiotici

Codice Prodotto	Descrizione	Prezzo Speciale Euro
A5955-100ML	Antibiotic antimycotic solution Stabilized (100x) 10.000U/ml Pen-10mg/ml Strep-25ug/ml Ampho	29.00
G1272-10ML	Gentamicin solution 10mg/ml	9.00
P0781-100ML	Penicillin-Streptomycin Solution (100x) 10.000U/ml Pen - 10mg/ml Strep	11.50
P0781-20ML	Penicillin-Streptomycin Solution (100x) 10.000U/ml Pen - 10mg/ml Strep	8.00
P3539-20ML	Penicillin-Streptomycin Solution, Gamma Irradiated	10.50
P4333-100ML	Penicillin-Streptomycin Solution Stabilized (100x) 10.000U/ml Pen - 10mg/ml Strep	13.00
A2942-50ml	Amphotericin B Solution (Fungizone) 250ug/ml	21.00
A5955-100ml	Antibiotic antimycotic solution Stabilized (100x) 10.000U/ml Pen-10mg/ml Strep-25ug/ml Ampho	29.00
G1397-10ml	Gentamicin solution cell culture tested	37.00
A1720-1G	G418 Disulfate salt Cell culture tested	66.00
N1638-100ml	Nystatin solution 10.000U/ml	31.50
T3397-20ml	Tylosin Solution 8mg/ml	9.50

Fattori di adesione e di dissociazione

Codice Prodotto	Descrizione	Prezzo Speciale Euro
L2020-1MG	Laminin	165.00
F1141-1MG	Fibronectin 0.1% solution (1mg/ml in 0.5M NaCl, 0.05M TRIS, pH 7,5)	85.00
P4707-50ML	Poly-L-Lysine solution - 0.01%, mol wt 70,000-150,000	48.00
P4832-50ML	Poly-L-Lysine solution - 0.01%, mol wt 150,000-300,000	49.00
C5914-100ML	Cell Dissociation Solution (1X)	21.50
T3924-100ML	Trypsin-EDTA Solution (1x) Cell Culture Tested 0.5g/L trypsin, 0.2g/L EDTA · 4Na in HBSS	11.50
T4049-100ML	Trypsin-EDTA Solution 0,25% - contains 2.5g/L trypsin, 0.2g/L EDTA · 4Na in HBSS	10.50
T4174-100ML	Trypsin-EDTA Solution (10x) Cell Culture Tested 5g/L trypsin, 2g/L EDTA · 4Na in 0.9% NaCl	13.50

Plastica Corning

Codice Prodotto	Descrizione	Prezzo Speciale Euro
C0677-1CS	Cell culture flasks, non-pyrogenic, 225 cm ² , canted neck, triangular shape	112.00
Z353442-100EA	Culture flasks with vented cap, 75 cm ²	165.00
Z353450-50EA	Culture flasks with vented cap, 150 cm ²	145.00
Z363278-200EA	Culture flasks with vented cap, 25 cm ²	172.00
Z371726-50EA	Corning cell culture flasks, 175 cm ² , angled neck, with vented cap	187.00
Z713813-25EA	Corning cell culture flasks, Size 225 cm ² angled neck with vent cap	131.00
Z716901-1CS	Corning Costar® cell culture flasks, Size 162 cm ² straight neck, vent cap	61.00
Z716936-1CS	Corning Costar® cell culture flasks, Size 25 cm ² angled neck	173.00
Z372099-100EA	Corning multiwell plates, tissue culture treated, 48 well, flat bottom	240.00
Z372102-50EA	Corning multiwell plates, tissue culture treated, 96 well, U-shaped bottom	95.00
Z711357-100EA	Corning Costar® cell culture plates, 12 well, flat bottom	168.00
Z711667-100EA	Corning Costar® cell culture plates, 24 well, flat bottom	152.00
Z712124-100EA	Corning Costar® cell culture plates, 6 well, flat bottom	147.00
Z712302-50EA	Corning Costar® cell culture plates, 96 well, flat bottom	88.00
Z712310-50EA	Corning Costar® cell culture plates, 96 well, V-bottom	102.00
C6296-500EA	Corning culture dishes, 35 mm × 10 mm, tissue-culture treated	142.00
C6421-500EA	Corning culture dishes, 60 mm × 15 mm, tissue-culture treated	157.00
C6546-500EA	Corning culture dishes, 100 mm × 20 mm, tissue-culture treated	240.00
C6671-60EA	Corning culture dishes, 150 mm × 25 mm, tissue-culture treated	90.00
Z371580-1000EA	Stripette Serological Pipettes, 1 mL	137.00
Z371599-1000EA	Stripette Serological Pipettes, 2 mL	157.00
Z371602-200EA	Stripette Serological Pipettes, 5 mL	45.00
Z371610-200EA	Stripette Serological Pipettes, 10 mL	45.00
Z371629-200EA	Stripette Serological Pipettes, 25 mL	89.00
Z371637-100EA	Stripette Serological Pipettes, 50 mL	105.00
Z717053-200EA	Corning Rectangular Canted Neck Flask, CellBIND™, 25cm ² , Vent Cap	304
Z717061-100EA	Corning Rectangular Canted Neck Flask, CellBIND™, 75cm ² , Vent Cap	230
Z717088-50EA	Corning Rectangular Canted Neck Flask, CellBIND™, 150cm ² , Vent Cap	190
Z717096-50EA	Corning Rectangular Canted Neck Flask, CellBIND™, 175cm ² , Vent Cap	206
Z717118-20EA	Corning Rectangular Canted Neck Flask, CellBIND™, 225cm ² , Vent Cap	131