

Material Safety Data Sheet

OSHA "Hazard Communication" (29 CFR 1910.1200)

NO-ZYME™

PBS Base, without calcium, without magnesium, without phenol red

CATALOG NO. 59226

Section I – Product Identification

Product Name:

NO-ZYME™, PBS Base, without calcium, without magnesium, without phenol red

Product Number:

59226

Product Classification:

Cell Culture Reagent

The subject formulation is a non-enzymatic cell dissociation solution in Phosphate Buffered Saline solution. With the exception of purified water, all ingredients are in concentrations of less than 1%.

Section II – Physical Data

Appearance:

Clear colorless solution

pH:

6.7 - 7.9

Section III – Hazardous Ingredients

Section Not Applicable.

Section IV – First Aid

In case of contact with eyes, flush thoroughly with water and contact a physician. In case of accidental swallowing, rinse the mouth with fresh water, provided the person is conscious. Contact a physician. In case of contact with skin, wash the affected area with soap and copious quantities of soap and water. Should irritation occur, contact a physician. In case of inhalation, remove to fresh air. Give oxygen if breathing becomes difficult. If not breathing, give artificial respiration. Contact a physician.

Section V – Fire and Explosion Hazard Data

Extinguishing Media:

Water spray, dry chemical powder or appropriate foam.

Section VI – Health (Toxicological) Hazard Data

This product is a potential irritant to eyes, respiratory system and skin. This product may also be harmful if ingested. Complete toxicological properties have yet to be determined.

United States

SAFC Biosciences, Inc.
13804 W. 107th Street
Lenexa, Kansas 66215
USA
Phone +1 913-469-5580
Toll free-USA 1 800-255-6032
Fax +1 913-469-5584
E-mail info-na@sial.com

Europe

SAFC Biosciences Ltd.
Smeaton Road, West Portway
Andover, Hampshire SP10 3LF
UNITED KINGDOM
Phone +44 (0)1264-333311
Fax +44 (0)1264-332412
E-mail info-eu@sial.com

Asia Pacific

SAFC Biosciences Pty. Ltd.
18-20 Export Drive
Brooklyn, Victoria 3025
AUSTRALIA
Phone +61 (0)3-9362-4500
Toll free-AUS 1 800-200-404
Fax +61 (0)3-9315-1656
E-mail info-ap@sial.com

Section VII – Stability and Reactivity

Stable. Hazardous Polymerization will not occur.

Section VIII – Special Protection Information

Eye Protection:

Safety glasses or goggles recommended.

Protective Gloves:

Chemical-resistant gloves recommended.

Respiratory Protection:

Protective mask recommended.

Ventilation:

Mechanical (general) or local exhaust.

Other Protection Equipment:

Safety shower and eye bath.

Section IX – Handling and Storage Precautions/Comments

Store at:

15 to 30 C. Protect from light.

Intended Use:

For research/laboratory use. THIS PRODUCT IS NOT INTENDED FOR HUMAN OR THERAPEUTIC USE.

Section X – Spill or Leak Procedures

Spill:

Wear rubber (surgical latex) or other chemical-resistant gloves. Absorb on sand, vermiculite or other absorbent material. Place in a closed container and hold for waste disposal. Wash area thoroughly after clean-up is complete.

Waste Disposal:

Follow all Federal, state and local regulations for chemical waste disposal.

Section XI – Disclaimer

The information, data and recommendations contained herein are believed to be accurate but may not be all-inclusive and should only be used as a guide. SAFC Biosciences makes no warranty of any kind whatsoever with respect thereto and disclaims all liability from reliance thereon. We reserve the right to revise this MSDS periodically as new information becomes available.

Warranty, Limitation of Remedies

SAFC Biosciences warrants to the purchaser for a period of one year from date of delivery that this product conforms to its specifications. Other terms and conditions of this warranty are contained in SAFC Biosciences' written warranty, a copy of which is available upon request. ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. In no case will SAFC Biosciences be liable for any special, incidental, or consequential damages arising out of this product or the use of this product by the customer or any third party based upon breach of warranty, breach of contract, negligence, strict tort, or any other legal theory. SAFC Biosciences expressly disclaims any warranty against claims by any third party by way of infringement or the like. THIS PRODUCT IS INTENDED FOR PURPOSES DESCRIBED ONLY AND IS NOT INTENDED FOR ANY HUMAN OR THERAPEUTIC USE.

Additional Terms and Conditions are contained in the product Catalog, a copy of which is available upon request.

NO-ZYME™ is a trademark of SAFC Biosciences, Inc.

© 2006 SAFC Biosciences, Inc.

Issued June 2006 M59226
0103 1005 0406

United States

SAFC Biosciences, Inc.
13804 W. 107th Street
Lenexa, Kansas 66215
USA

Phone +1 913-469-5580
Toll free-USA 1 800-255-6032
Fax +1 913-469-5584
E-mail info-na@sial.com

Europe

SAFC Biosciences Ltd.
Smeaton Road, West Portway
Andover, Hampshire SP10 3LF
UNITED KINGDOM

Phone +44 (0)1264-333311
Fax +44 (0)1264-332412
E-mail info-eu@sial.com

Asia Pacific

SAFC Biosciences Pty. Ltd.
18-20 Export Drive
Brooklyn, Victoria 3025
AUSTRALIA

Phone +61 (0)3-9362-4500
Toll free-AUS 1 800-200-404
Fax +61 (0)3-9315-1656
E-mail info-ap@sial.com

www.safcbiosciences.com