

Product Information

Yeastolate UF Solution 50X

200.0 g/L yeastolate UF

CATALOG NO. 58902C

Description

Prepared with 200.0 g/L of yeastolate ultrafiltrate in cell culture grade water and sterile filtered. Yeastolate UF is formulated specifically for use with insect cell culture media. Yeastolate UF is obtained by ultra filtration utilizing a 10 kD cutoff filter.

Precautions

Use aseptic technique when handling or supplementing this medium. This product is for further manufacturing use. THIS PRODUCT IS NOT INTENDED FOR HUMAN OR THERAPEUTIC USE.

Storage

Solution should be stored at 2 to 8 C, protected from light.

Indications of Deterioration

Solution should be clear and free of particulate and flocculent material. Do not use if solution is cloudy or contains precipitate. Other evidence of deterioration may include color change, pH shift and degradation of physical or performance characteristics. Do not use the product after the expiration date.

Preparation Instructions

Supplements Yeastolate UF Solution 50X at a working concentration using aseptic technique. Storage conditions and shelf life of the supplemented product may be affected by the nature of the supplements.

Characteristics

Appearance

Clear brown solution

Endotoxin

Refer to Certificate of Analysis

Osmolality (as supplied)

Refer to Certificate of Analysis

pH (as supplied)

Refer to Certificate of Analysis

Sterility

No microbial growth detected

United States

SAFC Biosciences, Inc.
13804 W. 107th Street
Lenexa, Kansas 66215
USA
Phone +1 913-469-5580
Toll free-USA 1 800-255-6032
Fax +1 913-469-5584
E-mail info-na@sial.com

Europe

SAFC Biosciences Ltd.
Smeaton Road, West Portway
Andover, Hampshire SP10 3LF
UNITED KINGDOM
Phone +44 (0)1264-333311
Fax +44 (0)1264-332412
E-mail info-eu@sial.com

Asia Pacific

SAFC Biosciences Pty. Ltd.
18-20 Export Drive
Brooklyn, Victoria 3025
AUSTRALIA
Phone +61 (0)3-9362-4500
Toll free-AUS 1 800-200-404
Fax +61 (0)3-9315-1656
E-mail info-ap@sial.com

Warranty, Limitation of Remedies

S AFC Biosciences warrants to the purchaser for a period of one year from date of delivery that this product conforms to its specifications. Other terms and conditions of this warranty are contained in S AFC Biosciences' written warranty, a copy of which is available upon request. ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. In no case will S AFC Biosciences be liable for any special, incidental, or consequential damages arising out of this product or the use of this product by the customer or any third party based upon breach of warranty, breach of contract, negligence, strict tort, or any other legal theory. S AFC Biosciences expressly disclaims any warranty against claims by any third party by way of infringement or the like. THIS PRODUCT IS INTENDED FOR PURPOSES DESCRIBED ONLY AND IS NOT INTENDED FOR ANY HUMAN OR THERAPEUTIC USE.

Additional Terms and Conditions are contained in the product Catalog, a copy of which is available upon request.

© 2006 S AFC Biosciences, Inc.

Issued December 2006 P58902
0805 1005 0406 0906

www.safcbiosciences.com

United States

S AFC Biosciences, Inc.
13804 W. 107th Street
Lenexa, Kansas 66215
USA

Phone +1 913-469-5580
Toll free-USA 1 800-255-6032
Fax +1 913-469-5584
E-mail info-na@sial.com

Europe

S AFC Biosciences Ltd.
Smeaton Road, West Portway
Andover, Hampshire SP10 3LF
UNITED KINGDOM

Phone +44 (0)1264-333311
Fax +44 (0)1264-332412
E-mail info-eu@sial.com

Asia Pacific

S AFC Biosciences Pty. Ltd.
18-20 Export Drive
Brooklyn, Victoria 3025
AUSTRALIA

Phone +61 (0)3-9362-4500
Toll free-AUS 1 800-200-404
Fax +61 (0)3-9315-1656
E-mail info-ap@sial.com