

Certificate of Analysis

Product number **E0409**Product name **Monoclonal anti EDEM3 Clone: EDEM3-1 produced in mouse; purified immunoglobulin**lot no: **069K4807**

Test	Specifications	Results
Country of origin	Israel	Israel
Form		
Clear solution in	0.01M Phosphate buffered saline pH 7.4	0.01M Phosphate buffered saline pH 7.4
Preservative	15mM Sodium Azide	15mM Sodium Azide
Stabilizer	None	None
Appearance		
Form	Liquid	Liquid
Clarity	Clear	Clear
Color	Colorless	Colorless
Odor	None	None
Protein Concentration by OD at 280nm		
IgG concentration	1 - 1.5 mg/ml	1.3 mg/ml
Immunoblot indirect ECL		
Cell extract/antigen	NIH-3T3 total cells extract NRK rat kidney cells extract	NRK rat kidney cells extract
Second antibody	A2304-HRP APA Mouse Fab ads/HuBovHor(gt) A9917- HRP APA Mouse Fab ads/HIgG (gt)	A2304-HRP APA Mouse Fab ads/HuBovHor(gt)
ECL-Substrate	ECL	ECL
Working concentration	1 - 2 µg/ml	2.000 µg/ml
MW detected	at ~120 kDa	at ~120 kDa
Storage conditions		
Storage Temperature:	-20°C	-20°C
QC release date:	30-Jun-2009	

Michal Gavish
Quality Assurance


Michal Gavish
Quality Assurance Manager