

# Licensing Requirements

## Sale of Controlled Substances

Orders for controlled substances can be purchased by internet ordering at [sigma-aldrich.com](http://sigma-aldrich.com) or in writing and are available only to those licensed by the Drug Enforcement Administration (DEA). For information on obtaining a DEA license, visit [www.DEADiversion.usdoj.gov](http://www.DEADiversion.usdoj.gov) or contact your local DEA Office. **Telephone orders cannot be accepted.**

Initial orders for all controlled substances must be accompanied by a photocopy of your institution's Federal Registration Form 223 (see adjacent column). We will keep this copy in our files for reference in filling future orders. To prevent delays in shipment, please ensure that our copy of your license is current and reference this license number on all DEA purchase orders.

### Your written purchase order must include:

- Your DEA registration number
- The 'ship to' address must exactly correspond to your name and address on the DEA registration
- A \$60.00 administrative fee is charged to cover the special handling and paperwork required by the DEA. The charge is the same, regardless of the number of items on the order. Please include this line item on your purchase order.

**Orders for Schedule I and II items** must also include a completed DEA Form 222 (see sample below). Schedule numbers for these products are listed on the following pages. Sigma-Aldrich's name and address must appear exactly as shown in the example below. Product names must appear exactly as listed in this catalog. **We cannot fill an order submitted on an altered or incomplete form. Erasures, type-overs, or use of white-out will invalidate the 222 Form.** If your name and address have changed, contact your local DEA office immediately. Shipment will be made only to the address printed on the form.

### FORM 223

CONTROLLED SUBSTANCES REGISTRATION CERTIFICATE			
UNITED STATES DEPARTMENT OF JUSTICE DRUG ENFORCEMENT ADMINISTRATION WASHINGTON, D.C. 20537			
<small>The Controlled Substance Act of 1970 reads in part as follows: Sec. 302. (a) A registration pursuant to section 302 to manufacture, distribute, or dispense a controlled substance may be suspended or revoked by the Attorney General if he determines that— (1) The registrant, knowingly, falsified any application pursuant to or obtained the registration— (2) He has been convicted of a felony under this title or title 48 or any other law of the United States or any State, territory, or any other possession of the United States, or (3) He has had his State license or registration suspended, revoked, or denied by competent State authority and is not being authorized by State law to engage in the manufacturing, distribution, or dispensing of controlled substances.</small>			
DEA REGISTRATION NUMBER	DEA REGISTRATION CLASS	DATE OF REGISTRATION	EXPIRES
AB1234567		MM/DD/YY	XX.XX
SCHEDULES	BUSINESS ACTIVITY	DATE ISSUED	
1, 2, 3, 3N, 4, 5	RESEARCHER	MM/DD/YY	
YOUR INSTITUTION 1 MAIN STREET TOWN, STATE XXXXX			
THIS CERTIFICATE IS NOT TRANSFERABLE ON CHANGE OF OWNERSHIP, CONTROL, LOCATION OR BUSINESS ACTIVITY			

### FORM 222

See Reverse of PURCHASERS Copy for Instructions		No order form may be issued for Schedule I and II substances unless a completed application form has been received. (21 CFR 1305.24).		OMB APPROVAL No. 1117-0010		
TO: (Name of Supplier) Sigma-Aldrich, Inc.			STREET ADDRESS 2425 S 2nd St.			
CITY and STATE St. Louis, MO, 63103		DATE Today's Date	TO BE FILLED IN BY SUPPLIER			
			SUPPLIER'S DEA REGISTRATION NO.			
TO BE FILLED IN BY PURCHASER						
LINE NO.	No. of Packages	Size of Package	Name of Item	National Drug Code	Packages Shipped	Date Shipped
1	1	250 mg	Cocaine hydrochloride			
2	2	1 g	Thebaine			
3	2	10 mg	Phencyclidine hydrochloride			
4						
5						
6						
7						
8						
9						
10						
3		NO. OF LINES COMPLETED		SIGNATURE OF PURCHASER OR HIS ATTORNEY OR AGENT		
Date Issued MM/DD/YY		DEA Registration No. AB1234567		Name and Address of Registrant		
Schedules 1, 2, 3, 3N, 4, 5		Registered as a RESEARCHER		No. of the Order Form 123456789		
				YOUR INSTITUTION 1 MAIN STREET TOWN, STATE ZIP		

DEA Form - 222 (Rev. 1/98)

U.S. OFFICIAL ORDER FORMS - SCHEDULES I & II  
DRUG ENFORCEMENT ADMINISTRATION  
SUPPLIER'S COPY 1

40147948

Instructions appear on the back of the form. Keep the blue copy and send the tan and green copy and carbons to supplier. (Sigma-Aldrich, Inc.)

- Fill in today's date.
- Fill in the name of supplier as Sigma-Aldrich, Inc., 2425 S 2nd St.
- Fill in columns marked "No. of Packages," "Size of Package," and "Name of Item." Use only one line per item ordered.
- Fill in "No. of lines completed."
- Supplied by the DEA. Do not change.
- Supplied by the DEA. Do not change.
- Sign with your Authorized Signature.
- Do not fill in. For Supplier use only.

# Licensing Requirements

## DEA Controlled Substances Classes I–V

Items marked (•) may not be exported from the USA

Cat. No.	DEA Class	Name	Cat. No.	DEA Class	Name
A8800	IV	Alprazolam	E3258	IV	Ethinamate
A6551	IV	Alprazolam- <i>d</i> <sub>5</sub>	E8512	II	• Ethylmorphine
A5880	II-N	• <i>D</i> -Amphetamine hemisulfate salt	F112	IV	(+)-Fenfluramine hydrochloride
A0922	II-N	• <i>D</i> -Amphetamine- <i>d</i> <sub>5</sub> sulfate salt	F113	IV	R(-)-Fenfluramine hydrochloride
A7505	III-N	1,4-Androstadiene-3,17-dione	F8507	IV	(±)-Fenfluramine hydrochloride
A8380	III-N	5 $\alpha$ -Androstan-17 $\beta$ -ol-3-one	F3886	II	Fentanyl citrate salt
A7755	III-N	5 $\alpha$ -Androstane-3 $\alpha$ ,17 $\beta$ -diol	F9261	IV	Flunitrazepam
B0375	IV	Barbital	F7751	III-N	Fluoxymesterone
B4147	II	• Benzoylcegonine hydrate	F103	IV	Flurazepam dihydrochloride
B142	II	Benzoylnorecgonine	H159	I	Heroin
B8263	III-N	Benzphetamine hydrochloride	H1005	III-N	Hexobarbital
B2934	I	• 1-Benzylpiperazine dihydrochloride	H7909	I	HU-210
B4144	IV	Bromazepam	H4516	II	Hydrocodone (+)-bitartrate salt
B159	I	(±)-1-(4-Bromo-2,5-dimethoxyphenyl)-2-ethanamine hydrochloride	H5136	II	Hydromorphone hydrochloride
B9275	III-N	Buprenorphine hydrochloride	H161	I	(±)-N-Hydroxy-3,4-methylenedioxyamphetamine
B9156	IV	Butorphanol (+)-tartrate salt	H162	II	<i>m</i> -Hydroxybenzoylcegonine
C155	II	(-)-2 $\beta$ -Carbomethoxy-3 $\beta$ -(4-iodophenyl)nortropane	H3635	I	• $\gamma$ -Hydroxybutyric acid sodium salt
C8759	IV	Carisoprodol	H163	II	<i>m</i> -Hydroxycocaine
C222	IV	Cathine hydrochloride	H2898	III-N	6 $\beta$ -Hydroxytestosterone
C3196	I	• S(-)-Cathinone hydrochloride	H4128	III-N	11 $\beta$ -Hydroxytestosterone
C124	II	$\beta$ -CFT naphthalenedisulfonate monohydrate	H9526	III-N	2 $\beta$ -Hydroxytestosterone
C8383	IV	Chloral hydrate	T133	III-N	Inactin <sup>®</sup> hydrate
C2517	IV	Chlordiazepoxide hydrochloride	J2753	I	JWH-133
C8414	IV	Clobazam	K1884	III-N	S-(+)-Ketamine hydrochloride
C1277	IV	Clonazepam	K2753	III-N	(±)-Ketamine hydrochloride
C0932	II	• Cocaehtylene	K113	III-N	Ketamine hydrochloride/xylazine hydrochloride solution
C8912	II	Cocaine free base	K4138	III-N	Ketamine hydrochloride/xylazine hydrochloride solution
C5776	II	Cocaine hydrochloride	K8250	III-N	11-Ketotestosterone
C139	II	Cocaine propyl ester hydrochloride	L7418	II	LAAM hydrochloride
C5901	II	Codeine	L5143	II	Levorphanol tartrate salt dihydrate
C3539	II	• Codeine- <i>d</i> <sub>5</sub> hydrochloride dihydrate	L1764	IV	(±)-Lorazepam
C156	II	<i>D</i> -CPT tartrate	L7007	I	• Lysergic acid diethylamide
D6787	II-N	(-)-Deoxyephedrine	M2017	IV	Mazindol
D7282	IV	Desmethyldiazepam	M3142	II	Meperidine hydrochloride
D0899	IV	Diazepam	M2392	IV	Meprobamate
E107	II	Ecgonidine methyl ester mesylate salt	M7655	III-N	Mesterolone
E5386	II	• Ecgonine methyl ester hydrochloride hydrate	M0267	II	(±)-Methadone hydrochloride
E3638	IV	Estazolam	M8750	II-N	(+)-Methamphetamine hydrochloride
43620	III-N	Estren			

# Licensing Requirements

## DEA Controlled Substances Classes I–V

Items marked (•) may not be exported from the USA

Cat. No.	DEA Class	Name	Cat. No.	DEA Class	Name
M3637	I	• Methaqualone hydrochloride	P0048	IV	Pemoline
M200	I	(±)-N-Methyl-1-(3,4-methylenedioxyphenyl)-2-butanamine hydrochloride	P127	IV	(+)-Pentazocine
M5037	I	• 2-(Methylamino)propiofenone hydrochloride	P134	IV	(-)-Pentazocine
M5626	III-N	17 $\alpha$ -Methylandrostan-17 $\beta$ -ol-3-one	P3761	II-N	Pentobarbital sodium salt
M6267	I	• (±)-3,4-Methylenedioxyamphetamine hydrochloride	P3029	II-N	• Phencyclidine hydrochloride
M139	I	S(+)-3,4-Methylenedioxyamphetamine hydrochloride	P1636	IV	Phenobarbital
M6403	I	• (±)-3,4-Methylenedioxyamphetamine hydrochloride	P5178	IV	Phenobarbital sodium salt
M1796	I	• (±)-3,4-Methylenedioxy-N-ethyl-amphetamine hydrochloride	P3654	IV	Prazepam
M2892	II-N	Methylphenidate hydrochloride	P2279	I	• Psilocin
M6810	II-N	D-threo-Methylphenidate hydrochloride	S1503	II-N	Secobarbital
M6935	II-N	L-threo-Methylphenidate hydrochloride	S1378	II-N	Secobarbital sodium salt
M7252	III-N	17 $\alpha$ -Methyltestosterone	S5147	II-N	• Secobarbital-d <sub>3</sub>
UC429	IV	Midazolam hydrochloride	B0500	IV	Sodium 5,5-diethylbarbiturate
M2419	IV	Midazolam maleate salt	S7132	III-N	Stanozolol
UC601	IV	Midazolam-(methyl,1,3 $\alpha$ ,4- <sup>13</sup> C <sub>4</sub> - <sup>15</sup> N) maleate salt	T8275	IV	Temazepam
M6940	IV	Modafinil	T1500	III-N	Testosterone
M6886	II	• Morphine 3- $\beta$ -D-glucuronide	T2000	III-N	Testosterone $\beta$ -D-glucuronide
M3528	II	• Morphine 6- $\beta$ -D-glucuronide hydrate	T8157	III-N	Testosterone $\beta$ -D-glucuronide sodium salt
M8777	II	Morphine sulfate salt pentahydrate	T9890	III-N	Testosterone 17-phenylpropionate
M3402	II	• Morphine-d <sub>3</sub> hydrochloride trihydrate	T3006	III-N	Testosterone enanthate
UC161	II	• Morphine-3,6-diglucuronide tetrahydrate	T6166	III-N	Testosterone isocaproate
N3785	II	Nabilone	T1875	III-N	Testosterone propionate
N100	III-N	Nalorphine hydrochloride	T2655	III-N	Testosterone-d <sub>3</sub>
N3889	IV	Nitrazepam	T2386	I	$\Delta^9$ -Tetrahydrocannabinol solution
N121	I	Normorphine	T2019	II	Thebaine
O5254	IV	Oxazepam	T9799	III-N	Thiamylal
O1378	II	Oxycodone hydrochloride	T1019	III-N	(±)-Thiopental
O0380	III-N	Oxymetholone	T3925	III-N	Trenbolone
			T9772	IV	Triazolam
			Z103	IV	Zolpidem
			Z4900	IV	Zopiclone