



3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

Product Information

DirectLoad™ Wide Range DNA Marker 50 bp - 10,000 bp

Product Number **D 7058**
Storage Temperature $-20\text{ }^{\circ}\text{C}$

TECHNICAL BULLETIN

Product Description

Suitable for use as an electrophoresis marker for DNA. Contains 16 bands ranging from 50 bp to 10,000 bp in the sizes listed below.

<u>DNA Sizes:</u> base pairs (bp)	
10,000	1,000
8,000	750
6,000	500
4,000	400
3,000	300
2,000	200
1,500	100
1,400	50

Supplied in 5x loading buffer containing marker dyes bromphenol blue and xylene cyanol FF. Ready for use in agarose gels.

Reagents

Storage Buffer: 2.5% ficoll, type 400, containing 0.0125% bromophenol blue, and 0.00625% xylene cyanol FF.

Storage/Stability

This product is shipped at ambient temperature. Marker is stable for 6 months when stored at $-20\text{ }^{\circ}\text{C}$.

Product Profile

Recommended load volume: 10 μl

Number of loads per vial: 100

Adjustments may be made for different well sizes and individual preferences.

Suitability Assay

10 μl of the DNA ladder solution was loaded onto two agarose submarine type minigels in 1x TBE (Product No. T 9525), a 0.8% (w/v) gel used to resolve the larger bands and a 2.0% (w/v) gel used to resolve the smaller bands. The gels were subjected to electrophoresis at 80 volts until the bromophenol blue tracking dye migrated at least two-thirds of the way down the gel. After staining for 15-20 minutes in 5 $\mu\text{g/ml}$ ethidium bromide and destaining with water for 15-20 minutes, all the bands were clearly resolved and the pattern was consistent with the indicated DNA sizes.

JLL/JWM 10/03

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.