



3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

Product Information


TESTOSTERONE STEROID

Methanol Solution

Product Number T 5411
Lot Number 073K8809
CAS Number [58-22-0]
Concentration 1.02 mg Testosterone/mL HPLC grade
1,2- dimethoxyethane (conc. Verified
by UV)
Molecular Formula C₁₉H₂₈O₂
Molecular Weight 288.4
DEA Class Exempt preparation of Class III


Synonyms 4-Androsten-17 β -ol-3-one; 17 β -Hydroxy-4-androsten-3-one; trans-Testosterone
Stability If stored at 2-8°C in an air tight container, protected from light, decomposition of the product is less than 1% in 12 months. After opening, concentration may change due to loss of solvent.
Expiration Date April 2006
Storage 2-8°C; After opening, transfer contents to small vial provided for your convenience.

70 eV Electron Ionization Mass Spectrum



Hewlett-Packard 5890 Series II Gas Chromatograph
Hewlett-Packard 5971 Mass Selective Detector
Hewlett-Packard G1034C MS ChemStation (HP-DOS series)


FT-IR



Mattson Galaxy 3020 FT-IR


TESTOSTERONE STEROID

Methanol Solution
Product Number T 5411
Lot Number 073k8809



Ultraviolet Spectrum


Peak	241.0 nm
Absorbance	0.629
Solvent	Methanol
Dilution	1:99 (v/v)



Bio-Tek Uvikon XL

Capillary Gas Chromatography

Column	Supelco SPB-1 (Cat. No. 2-4162)
I.D.	0.20 mm
Length	15 m
Film Thickness	0.20 μ m
Oven Temperature	150°C (2 min.), then 15°/min. to 300°C, hold 18 min.
Injector Temperature	250°C, Split
Detector	Hewlett-Packard 5971 Mass Selective Detector (70 eV, 40-500 m/z)



Hewlett-Packard 5890

T 5411/073k8809/08/21/03

This product is not for *in vitro* diagnostic procedures. For R&D use only. Not for drug, household or other uses.
Sigma brand products are sold through Sigma-Aldrich, Inc.
Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications.
Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply.
Please see reverse side of the invoice or packing slip.