

	D0547	D0697	D2906	D6421	D6434	D8900	D8062	D8437	D9785
	[powder]	[1×]	[powder]	[1×]	[1×]	[powder]	[1×]	[1×]	[powder]
COMPONENT	g/L	g/L	g/L	g/L	g/L	g/L	g/L	g/L	g/L
Vitamins									
D-Biotin	0.000035	0.000035	0.000035	0.000035	0.000035	0.000035	0.000035	0.000035	0.000035
Choline Chloride	0.00898	0.00898	0.00898	0.00898	0.00898	0.00898	0.00898	0.00898	0.00898
Folic Acid	0.00266	0.00266	0.00266	0.00265	0.00266	0.00266	0.00266	0.00266	0.00266
myo-Inositol	0.0126	0.0126	0.0126	0.0126	0.0126	0.0126	0.0126	0.0126	0.0126
Niacinamide	0.00202	0.00202	0.00202	0.00202	0.00202	0.00202	0.00202	0.00202	0.00202
D-Pantothenic Acid • ½Ca	0.00224	0.00224	0.00224	0.00224	0.00224	0.00224	0.00224	0.00224	0.00224
Pyridoxal • HCl	0.002	—	0.002	—	—	0.002	0.002	—	0.002
Pyridoxine • HCl	0.000031	0.002031	0.000031	0.002031	0.002031	0.000031	0.002031	0.002031	0.000031
Riboflavin	0.000219	0.000219	0.000219	0.000219	0.000219	0.000219	0.000219	0.000219	0.000219
Thiamine • HCl	0.00217	0.00217	0.00217	0.00217	0.00217	0.00217	0.00217	0.00217	0.00217
Vitamin B ₁₂	0.00068	0.00068	0.00068	0.00068	0.00068	0.00068	0.00068	0.00068	0.00068
Other									
D-Glucose	3.15	3.15	3.15	3.15	3.15	3.15	3.15	3.15	3.15
HEPES	—	3.5745	3.5745	3.5745	3.5745	3.5745	—	3.5745	3.5745
Hypoxanthine	0.0021	0.00244	0.0021	0.00244	0.00244	0.0021	0.00244	0.00244	0.0021
Linoleic Acid	0.000042	0.000042	0.000042	0.000042	0.000042	0.000042	0.000042	0.000042	0.000042
Phenol Red • Na	0.00863	0.00863	—	0.00863	—	0.00863	0.00863	0.00863	—
Putrescine • 2HCl	0.000081	0.000081	0.000081	0.000081	0.000081	0.000081	0.000081	0.000081	0.000081
Pyruvic Acid • Na	0.11	0.055	0.055	0.055	0.055	0.055	0.055	0.055	0.055
DL-Thioctic Acid	0.000105	0.000105	0.000105	0.000105	0.000105	0.000105	0.000105	0.000105	0.000105
Thymidine	0.000365	0.000365	0.000365	0.000365	0.000365	0.000365	0.000365	0.000365	0.000365
ADD									
NaHCO ₃	1.2	—	1.2	—	—	1.2	—	—	1.2
CaCl ₂ • 2H ₂ O	—	—	—	—	—	—	—	—	0.1545
L-Glutamine	—	—	—	0.365	0.365	—	—	—	0.365
L-Leucine	—	—	—	—	—	—	—	—	0.05905
L-Lysine • HCl	—	—	—	—	—	—	—	—	0.09125
MgCl ₂ • 6H ₂ O	—	—	—	—	—	—	—	—	0.0612
MgSO ₄	—	—	—	—	—	—	—	—	0.04884
L-Methionine	—	—	—	—	—	—	—	—	0.0172

RC,BG,JS,JG,GS,JF,LCM,MAM 12/20-1