

XXXXXX

7.76072.0004 01/2025

1.16996

Supelco®

sigmaaldrich.com

50 Tests


Reflectoquant®

pH Test for RQflex® 20

pH-Test für RQflex® 20

pH 4.0 - 9.0

Reaction time: 10 sec



For determination in weakly buffered solutions see Instruction for Use

Bestimmung in schwach gepufferten Lösungen s. Gebrauchsanweisung

Please consult Instruction for Use for further information and observe the RQflex® manual.



For IfU please scan code with My M Safety App or go to sigmaaldrich.com



©2025

Store cool and dry • (15 - 25 °C) • Kühl und trocken lagern

Lot

min. shelf life (YYYY/MM/DD)

Merck KGaA, 64271 Darmstadt, Germany
EMD Millipore Corporation, Burlington MA 01803, USA
MilliporeSigma Canada Ltd., 2149 Winston Park Dr, Oakville,
Ontario, L6H 6J8, Canada