


Product Information

BUPRENORPHINE HYDROCHLORIDE

Methanol Solution


Product Number	B 7536	Synonyms	21-Cyclopropyl-7 α -(S)-1-hydroxy-1,2,2-trimethylpropyl]-6,14-endo-ethano-6,7,8,14-tetrahydrooripavine hydrochloride
Lot Number	93K8806	Stability	If stored at < 0°C in an air tight container, protected from light, decomposition of the product is less than 2% in 12 months. After opening, concentration may change due to loss of solvent.
CAS Number	[53152-21-9]	Expiration Date	June 2008
Concentration	1.12 mg Burpenorphine Hydrochloride (equivalent to 1.04 mg free base)/mL GC grade methanol (conc. verified by UV)	Storage	< 0°C; After opening, transfer contents to small vial provided for your convenience.
Molecular Formula	C ₂₉ H ₄₁ NO ₄ • 3HCl	DEA Class	Exempt preparation of
Molecular Weight	504.1		

70 eV Electron Ionization Mass Spectrum



Hewlett-Packard 5890 Series II Gas Chromatograph
 Hewlett-Packard 5971 Mass Selective Detector
 Hewlett-Packard G1034C MS ChemStation (HP-DOS series)

FT-IR




BUPRENORPHINE HYDROCHLORIDE

Methanol Solution


Product Number B 7536

Lot Number 93K8806



Ultraviolet Spectrum


Peak	286.5 nm
Absorbance	0.725
Solvent	0.2 N H ₂ SO ₄
Dilution	1:4 (v/v)



Bio-Tek Uvikon XL

Capillary Gas Chromatography

Column Supelco SPB-1 (Cat. No. 2-4162)
I.D. 0.20 mm **Length** 15 m **Film Thickness** 0.20 μm
Oven Temperature 50°C (2 min.), then 15°/min. to 300°C,
hold 11 min.
Injector Temperature 250°C, Split
Detector Hewlett-Packard 5971
Mass Selective Detector (70 eV, 40-500 m/z)



Hewlett-Packard 5890

B 7536/93K8806/10/23/03

This product is not for *in vitro* diagnostic procedures. For R&D use only. Not for drug, household or other uses.

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications.

Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply.

Please see reverse side of the invoice or packing slip.