

## 82265 m-CP selective Supplement II

Filter sterilized 0.5 % solution of phenolphthalein diphosphate recommended by the Directive of the Council of the European Union 98/83/EC for the selective isolation of *Clostridium perfringens*.

### Composition

(per vial, is sufficient for 500 ml medium)

Phenolphthalein diphosphate 0.05g

Distilled water 10ml

### Directions

Warm up the refrigerated 0.5 % solution of phenolphthalein diphosphate to room temperature and add aseptically 10 ml. of solution to 485 ml sterile molten M-CP Agar Basis (Cat. No. 75605; cooled to < 50°C) along with rehydrated contents of one vial of m-CP-Selective-Supplement I (Cat. No. 51962). Mix well before pouring into sterile petri plates.

### Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

