


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
N-Boc-4-piperidineacetaldehyde - 97%

Product Number: 680214
CAS Number: 142374-19-4
MDL: MFCD03425258
Formula: C₁₂H₂₁NO₃
Formula Weight: 227.3 g/mol



TEST

Specification

| | |
|--|--------------------------|
| Appearance (Color) | White to Tan |
| Appearance (Form) | Conforms to Requirements |
| Crystals, Powder, Crystalline Powder and/or Chunks | |
| Infrared spectrum | Conforms to Structure |
| Carbon | 61.2 - 65.6 % |
| Nitrogen | 5.8 - 6.5 % |
| Purity (GC) | ≥ 96.5 % |

Specification: PRD.0.ZQ5.10000012314

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.