

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)


## Product Specification

Product Name:

Hydrogen peroxide solution - contains inhibitor, 30 wt. % in H<sub>2</sub>O, meets USP testing specifications

Product Number:

H3410



MDL:

MFCD00011333

Formula:

H<sub>2</sub>O<sub>2</sub>

Formula Weight:

34.01 g/mol

Storage Temperature:

2 - 8 °C

TEST	Specification
------	---------------

Identity	Pass
Acidity	Pass
Chloride Content	≤ 0.005 %
Non-volatile Matter	≤ 30 mg
Heavy Metals	≤ 5 ppm
Miscellaneous Assay	≤ 0.05 %
Limit of Preservative	
Assay	≤ 32.0 %

Specification Date : 04/14/2011

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.