

Product Specification

Product Name:

Antibiotic Antimycotic Solution (100×), Stabilized - with 10,000 units penicillin, 10 mg streptomycin and 25 µg amphotericin B per mL, 0.1 µm filtered, BioReagent, suitable for cell culture

Product Number: A5955

Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Suspension
Appearance (Color)	Yellow
Osmolality	
Potency - Penicillin (U/ml)	10000 - 12000
Potency Streptomycin	10.0 - 12.0 mg/ml
Potency Amphotericin B	25.0 - 30.0 µg/ml
Endotoxin Level at 10ml/L	≤ 0.50 EU/ml
Cell Culture Test Cell Line	Hep-2 Human Cells
Cell Culture Test	≥ 50 %
Expiration Date Period	-----
24 months	

Specification: PRE.4.ZQ5.10000013851

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

