

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Fibroblast Growth Factor-Basic Heparin Stabilized human - FGF-Basic, recombinant, expressed in E. coli, sterile-filtered, aqueous solution, suitable for cell culture

Product Number: **F9786**  
CAS Number: 106096-93-9  
MDL: MFCD00081382

Storage Temperature: 2 - 8 °C

TEST	Specification
------	---------------

pH	7.1 - 7.7
at RT	
Endotoxin Level	≤ 10.0 EU/ml
Sterility by USP guidelines	Negative
Growth Factor Bioassay	0.03 - 3.00 ng/ml
Chapter 4(D) - Heat	Conforms

Product meets European Union requirements for treated technical blood products. Form of treatment heat treated at 65 deg C for 3 hours.

Specification: PRD.2.ZQ5.10000038134

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

