

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-HA antibody produced in rabbit - affinity isolated antibody, buffered aqueous solution

Product Number:

H6908

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	0.5 - 0.8 mg/ml
WB-Cell Line/Tissue Extract	293-T Cells Exp N-Terminal HA
WB Working Concentration	0.5 - 0.8 µg/ml
WB-Cell Line/Tissue Extract(2)	293-T Cells Exp C-Terminal HA
WB-Working Concentration	0.5 - 0.8 µg/ml
IP - Cell /Tissue Lysate	293-T Cells Exp N-Ter or C-Ter HA
IP - Antibody Precipitation	2.5 - 4.0 µg
ICC/IF Cells	293-T Cells Exp N-Ter or C-Ter HA
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Working Concentration	10 - 20 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016400

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.