

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
(24R)-24,25-Dihydroxyvitamin D3 solution - 100 µg/mL in ethanol, ≥97% (CP)

Product Number: **809748**

Storage Temperature: -20 °C

TEST	Specification
Appearance (Clarity)	Clear
Appearance (Color)	Colorless
Appearance (Form)	Solution
Purity (HPLC)	≥ 97 %
Proton NMR Spectrum	Conforms to Structure
Concentration	90.0 - 110.0 µg/ml
Mass Spectrometry	Conforms to Structure

Specification: PRD.0.ZQ5.10000068500

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.