


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
(-)-B-METHOXYDIISOPINOCAMPHEYLBORANE

Product Number: **317047**
 CAS Number: 85134-98-1
 MDL: MFCD00074809
 Formula: C₂₁H₃₇BO
 Formula Weight: 316.33 g/mol



TEST	Specification
Appearance (Color)	White
Appearance (Form)	Conforms to Requirements
CRYSTALS, POWDER, SOLID, WAXY CRYSTALS, WAXY SOLID, WAXY POWDER AND/OR WAXY CLUMPS	
Initial Melting Point	≥ 50.0 °C
Final Melting Point	≤ 65.0 °C
Infrared spectrum	Conforms to Structure
OPTICAL ROTATION	-76.0 - -65.0
DEGREES (C= 1%, ETHER)	

Specification: PRD.0.ZQ5.10000104201

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

