

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Mouse IgG (whole molecule)-Peroxidase antibody produced in rabbit - IgG fraction of antiserum, buffered aqueous solution

Product Number:

A9044

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Brown
IgG Concentration (OD 280nm)	10.0 - 20.0 mg/ml
Molar Ratio P/E	0.6 - 1.5
ELISA - Titer	1:40,000-1:50,000
WB-Cell Line/Tissue Extract	Hela Cells
WB Titer	1:80,000-1:160,000
IHC - Tissue	Human Appendix or Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:200-1:400
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000016374

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.