


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Tyrphostin AG 1478 -  $\geq 98\%$ Product Number: **T4182**  
CAS Number: 175178-82-2Formula: C<sub>16</sub>H<sub>14</sub>ClN<sub>3</sub>O<sub>2</sub>  
Formula Weight: 315.75 g/mol  
Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Color)	White
Appearance (Form)	Powder
Proton NMR spectrum	Conforms to Structure
Water (by Karl Fischer)	$\leq 5\%$
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
10 mg/ml DMSO:MeOH (1:1)	
Purity (HPLC)	$\geq 98\%$

Specification: PRD.0.ZQ5.10000045590

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.