


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Piroxicam - meets USP testing specifications

Product Number: P0847
CAS Number: 36322-90-4
MDL: MFCD00057317
Formula: C₁₅H₁₃N₃O₄S
Formula Weight: 331.35 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Identity	Pass
Water (by Karl Fischer)	≤ 0.5 %
Residue on ignition (Ash)	≤ 0.3 %
Heavy Metal	≤ 0.005 %
Residual Solvents USP 467	Meets Requirements
Assay	97.0 - 103.0 %

Specification: PRD.0.ZQ5.10000066767

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.