

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
ECOSURF™ EH-9Product Number: **STS0006**  
CAS Number: 64366-70-7Formula:  $C_8H_{18}O.(C_3H_6O)_x.(C_2H_4O)_y$ 

| TEST  | Specification         |
|---|-----------------------|
| Appearance (Form)   | Liquid                |
| <sup>1</sup> H NMR Spectrum   | Conforms to Structure |
| Color   | ≤ 150                 |
| Pt-Co, 40°C   |                       |
| Water   | ≤ 0.5 % wt            |
| Cloud Point   | 62 - 67 °C            |
| 10%, Water  |                       |
| pH  | 5.0 - 7.5             |
| 1%, Water   |                       |
| Trademark   | Confirmed             |
| ECOSURF is a trademark of The Dow Chemical Company ("Dow")<br>or an affiliated company of Dow |                       |

Specification: PRD.1.ZQ5.10000082649

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.