

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Hydrogen fluoride pyridine - pyridine ~30 %, hydrogen fluoride ~70 %

**Product Number:****184225**

CAS Number:

62778-11-4

MDL:

MFCD00012436

Formula:


C<sub>5</sub>H<sub>6</sub>FN

Formula Weight:

99.11 g/mol

Storage Temperature:

-20 °C

**TEST****Specification**

Appearance (Color)

Colorless to Light Yellow and Colorless  
to Light Brown

Appearance (Form)

Liquid

Gravimetric Analysis

63.8 - 69.5 %

% F With Lead Acetate

Note

Note

May Contain or Form Low Levels of Calcium Fluoride During Storage.

Presence of This Does Not Impact the Specification Values.

Recommended Retest Period

60 Months

Specification: PRD.2.ZQ5.10000011080

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.