

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Anisyl phenylacetate -  $\geq 97\%$

Product Number: **W374008**

CAS Number: 102-17-0

Formula: C<sub>16</sub>H<sub>16</sub>O<sub>3</sub>

Formula Weight: 256.30 g/mol

TEST	Specification
Appearance (Color)	Colorless to Pale Yellow
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.557 - 1.561
Infrared spectrum	Conforms to Structure
Purity (GC)	$\geq 97.0 \%$
Arsenic (As)	$\leq 3 \text{ ppm}$
Cadmium (Cd)	$\leq 1 \text{ ppm}$
Mercury (Hg)	$\leq 1 \text{ ppm}$
Lead (Pb)	$\leq 10 \text{ ppm}$

Specification: PRD.0.ZQ5.10000043797

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.