

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Monoclonal Anti-Human IgG1-FITC antibody produced in mouse - clone 8c/6-39, purified immunoglobulin, buffered aqueous solution

Product Number:

F0767

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Yellow
IgG Concentration (OD 280nm)	2.0 - 4.0 mg/ml
F/P Molar Ratio	3.0 - 8.0
Dot Blot-Titer	1:64-1:128
P-IMFA Particle Immunofl Assay	-----
P-IMFA Agarose Beads Coating A	Human IgG1 or Human IgG
P-IMFA Titer	1:32-1:64
Recommended Retest Period	-----
3 Years	

Specification: PRE.0.ZQ5.10000015581

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.