


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Bis[4-(glycidyloxy)phenyl]methane - mixture of isomers

Product Number: **900198**
CAS Number: 2095-03-6



Formula: C₁₉H₂₀O₄
Formula Weight: 312.37 g/mol
Storage Temperature: 2 - 8 °C

| TEST | Specification |
|------|---------------|
|------|---------------|

| | |
|-----------------------------|---|
| Appearance (Color) | White to Yellow to Brown and Colorless to Yellow to Brown |
| Appearance (Form) | Liquid or Solid |
| Infrared Spectrum | Conforms to Structure |
| ¹ H NMR Spectrum | Conforms to Structure |
| Purity (HPLC) | ≥ 88.0 % |
| Mixture of Isomers | |

Specification: PRD.1.ZQ5.10000077411

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.