

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-hFBXW7 antibody, Mouse monoclonal - clone FB407, purified from hybridoma cell culture

Product Number:

F2055

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	2.0 - 2.5 mg/ml
WB-Cell Line/Tissue Extract	A431 Human epithelial carcinoma cells
WB-Working Concentration	5 - 10 µg/ml
ICC/IF Cells	A431 or HeLa Cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Working Concentration	10 - 20 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.1.ZQ5.10000018828

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.