


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Divinylbenzene - technical grade, 80%

**Product Number:** 414565  
**CAS Number:** 1321-74-0  
**MDL:** MFCD01778656  
**Formula:** C<sub>10</sub>H<sub>10</sub>  
**Formula Weight:** 130.19 g/mol  
**Storage Temperature:** 2 - 8 °C



TEST	Specification
Appearance (Color)	Colorless to Pale Yellow
Appearance (Form)	Liquid
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 79.0 %
Mixture of Isomers	
Color Test	≤ 4
Gardner Value	
Miscellaneous Assay	≤ 20 ppm
Polymer Content	
4-T-Butylcatechol	≤ 1100 ppm
Isomer	
M-Divinylbenzene	
Isomer	
P-Divinylbenzene	
Isomer	
Ethylvinylbenzene	
Isomer	
Diethylbenzene	
Isomer	
Naphthalene	

Specification: PRD.1.ZQ5.1000004932

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.