

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Monoclonal Anti-Transportin 1 antibody produced in mouse – clone D45, purified immunoglobulin, buffered aqueous solution

Product Number:

T0825

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)

Liquid

Appearance (Turbidity)

Clear to Slightly Hazy

Appearance (Color)

Colorless

IgG Concentration (OD 280nm)

0.5 - 0.8 mg/ml

WB-Cell Line/Tissue Extract

Hela Cells Nuclear Fr.

WB-Working Concentration

0.1 - 0.2 µg/ml

Recommended Retest Period

4 Years

Specification: PRE.0.ZQ5.10000018486

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.