

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com


Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Hexylene glycol - BioXtra, ≥99% (GC)

Product Number: M9671
CAS Number: 107-41-5
MDL: MFCD00004547
Formula: C₆H₁₄O₂
Formula Weight: 118.17 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid or Viscous Liquid
Appearance (Turbidity)	Clear
Residue on ignition (Ash)	≤ 0.1 %
Chloride (Cl)	Pass
< or = 0.05%	
Sulfate	Pass
< or = 0.05%	
Aluminum (AL)	≤ 0.0005 %
Phosphorus (P)	≤ 0.0005 %
Lead (Pb)	≤ 0.001 %
Iron (Fe)	≤ 0.0005 %
Copper (Cu)	≤ 0.0005 %
Zinc (Zn)	≤ 0.0005 %
Calcium (Ca)	≤ 0.0005 %
Magnesium (Mg)	≤ 0.0005 %
Sodium (Na)	≤ 0.005 %
Potassium (K)	≤ 0.005 %
Ammonia (NH ₄)	≤ 0.05 %
Purity (GC)	≥ 99 %
Recommended Retest Period	-----
6 Years	

Specification: PRD.1.ZQ5.10000012759

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.