

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

ANTI-FLAG® antibody produced in rabbit - affinity isolated antibody, buffered aqueous solution

Product Number:

F7425

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless to Faint Yellow
IgG Concentration (OD 280nm)	0.8 - 1.0 mg/ml
Dot Blot- working concentration	1.0 - 2.5 µg/ml
WB-Cell Line/Tissue Extract	E.Coli Exp FLAG Tagged Prot.
WB Working Concentration	1.0 - 2.5 µg/ml
IP - Cell /Tissue Lysate	FLAG Tagged Protein
IP - Antibody Precipitation	4 - 8 µg
ICC/IF Cells	293-T Cells Exp FLAG Tagged Prot.
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Working Concentration	5 - 10 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.2.ZQ5.10000015515

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.