

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Neuraminidase from *Vibrio cholerae* - Type III, buffered aqueous solution, 0.2 µm filtered, 1-5 units/mg protein (Lowry, using NAN-lactose)

Product Number:

N7885

CAS Number:

9001-67-6

Storage Temperature:

2 - 8 °C

TEST	Specification
------	---------------

Appearance (Form)

Clear Solution

Conforms

Protein Content (Method)

Enzym. Assay (Spec. Activity)

Enzym. Assay (Contam.1 Name)

Enzym.Assay (Activity contm.1)

Enzym. Assay (Contam.2 Name)

Enzym.Assay (Activity contm.2)

Microbial Contamination

Handling Precautions

Recommended Retest Period

2 Years

Lowry

1.00 - 5.00 U/mgP

Protease

≤ 0.50 U/mgP

NAN-Aldolase

≤ 0.10 U/mgP

Pass

Do Not Freeze

-----

Specification: PRE.4.ZQ5.10000001202

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.