


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Azelaoyl PAF - 10 mg/mL in ethanol

Product Number: **A6850**



MDL: MFCD03412018
Formula: C₃₃H₆₆NO₉P
Formula Weight: 651.85 g/mol
Storage Temperature: -20 °C

TEST	Specification
Purity (TLC)	≥ 98 %
Infrared spectrum	Conforms to Structure
Formulation 10 mg/ml in EtOH	

Specification: PRD.0.ZQ5.10000056847

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.