



3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

Product Information

Adenosine 5'-triphosphate disodium salt SigmaUltra

Product Number **A 7699**
Storage Temperature $-0\text{ }^{\circ}\text{C}$

CAS# 987-65-5
Synonym: ATP

Product Description

Molecular Formula: $\text{C}_{10}\text{H}_{14}\text{N}_5\text{Na}_2\text{O}_{13}\text{P}_3$
Molecular Weight: 551.1 (anhydrous)
 pK_a : 4.0 (amino group); 6.5 (secondary phosphate)
 λ_{max} : 259 nm
Extinction Coefficient: $E^{\text{mM}} = 15.4$ (259 nm in 100 mM phosphate buffer, pH 7.0).

Adenosine 5'-triphosphate (ATP) and its phosphate bonds are the basic components of energy exchange in many biological systems. The purification and crystallization of ATP from equine muscle led to the entry of the Sigma Chemical Company into the research biochemical field. Sigma became the first to offer stable, crystalline ATP with a purity approaching 100%. The initial products were isolated from muscle tissue and precipitated with ethanol.¹ Currently, this product is isolated from a microbial source and is produced via a fermentation process. No chemical phosphorylation is involved.

Trace elemental analyses have been performed on the SigmaUltra ATP. The certificate of analysis provides lot specific results. SigmaUltra ATP is for applications, which require tight control of elemental content.

This preparation of ATP is recommended for use as an ATP standard in bioluminescence assays. The recommended ATP products for standards in bioluminescence experiments are sodium salts of ATP: Product No. A 7699 (packaged in bulk, to be weighed by the user) and Product Code FL-AAS, preweighed vials equivalent to 1.0 mg of ATP (2 μmole).

ATP has intrinsic metal binding affinity. The binding constant for various metals are (given as per mole):²
 Mg^{2+} (9,554), Na^+ (13), Ca^{2+} (3,722),
 K^+ (8), Sr^{2+} (1,381), Li^+ (25).

Precautions and Disclaimer

For Laboratory Use Only. Not for drug, household or other uses.

Preparation Instructions

ATP is soluble in water (50 mg/ml), yielding a clear, colorless solution. This solution is mildly acidic (pH approximately 3.5).

Storage/Stability

The product is routinely shipped at ambient temperature without degradation. It is recommended to store the product at $-0\text{ }^{\circ}\text{C}$ with desiccation. A very slow dismutation occurs in the powdered product with 2 ATP molecules forming ADP and adenosine 5'-tetrakisphosphate. A decomposition of less than 0.5% per year is observed. The product is stable for at least 2 years.

Aqueous solutions of ATP are stable for months when frozen at $-15\text{ }^{\circ}\text{C}$ and for approximately one week at $0\text{ }^{\circ}\text{C}$. ADP is the first hydrolysis product formed, with additional hydrolysis leading to the formation of AMP. However, ATP solutions are only stable for several hours at $0\text{ }^{\circ}\text{C}$ when dissolved in a trichloroacetic acid solution. In alkaline solution, it rapidly decomposes to inorganic pyrophosphate and adenosine 5'-phosphate even at $0\text{ }^{\circ}\text{C}$.³

References

- Berger, L., *Biochim. Biophys. Acta*, **20**, 23 (1956).
- Wilson, J.E., et al., Chelation of divalent cations by ATP, studied by titration calorimetry. *Anal. Biochem.*, **193**, 16 (1991).
- Data for *Biochemical Research*, 3rd ed., Dawson, R.M.C., et al., Oxford University Press (New York, NY: 1986) p. 78.

MWM/NSB/MAM 10/02

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.