

| Cat# | Product | Pack Size | INR Price |
|---|---|-----------|-----------|
| LC-MS Chromasolv Solvents | | | |
| 34967 | Acetonitrile LC-MS Chromasolv | 1 lit | 3,644 |
| | | 2.5 lit | 5,684 |
| 34966 | Methanol LC-MS Chromasolv | 1 lit | 1,487 |
| | | 2.5 lit | 1,611 |
| 34965 | 2-Propanol LC-MS Chromasolv | 1 lit | 2,451 |
| | | 2.5 lit | 5,103 |
| LC-MS Chromasolv Solvent Blends | | | |
| 34669 | Acetonitrile with 0.1% ammonium acetate LC-MS Chromasolv | 2.5 lit | 7,820 |
| 34670 | Methanol with 0.1% ammonium acetate LC-MS Chromasolv | 2.5 lit | 2,961 |
| 34976 | Acetonitrile with 0.1% TFA LC-MS Chromasolv | 2.5 lit | 7,951 |
| 34974 | Methanol with 0.1% TFA LC-MS Chromasolv | 2.5 lit | 2,961 |
| 34668 | Acetonitrile with 0.1% Formic acid LC-MS Chromasolv | 2.5 lit | 8,448 |
| 34671 | Methanol with 0.1% Formic acid LC-MS Chromasolv | 2.5 lit | 2,961 |
| Mobile Phase Additives for LC-MS | | | |
| 73594 | Ammonium acetate, puriss. p.a., for mass spectroscopy, ≥99.0% | 25g | 7,576 |
| 55674 | Ammonium formate, eluent additive for LC-MS | 50 g | 10,289 |
| 56302 | Formic acid, eluent additive for LC-MS | 10 x 1 ml | 3,411 |
| 56302 | Formic acid, eluent additive for LC-MS | 50 ml | 2,511 |
| 49199 | Acetic acid, eluent additive for LC-MS | 50 ml | 2,475 |
| 40867 | Ammonium bicarbonate, eluent additive for LC-MS | 50 g | 2,397 |
| 40967 | Trifluoroacetic acid, eluent additive for LC-MS | 10 x 1 ml | 8,772 |
| LC-MS Flush Solution | | | |
| 34689 | Chromasolv Flush Solution, water:2propanol, 50:50 | 1 lit | 1,490 |
| LC-MS Post Column Splitters | | | |
| 56626-U | HPLC Flow Splitter-Fixed Split Ratio 5:1, Post Column | 1 ea | 85,231 |
| 56627-U | HPLC Flow Splitter-Fixed Split Ratio 3:1, Post Column | 1 ea | 85,231 |
| 56625-U | HPLC Flow Splitter-Fixed Split Ratio 10:1, Post Column | 1 ea | 85,231 |
| 56629-U | HPLC Flow Splitter-Adjustable 1:1 - 20:1, Post Column (1) | 1 ea | 166,332 |
| Ascentis LC-MS HPLC Columns | | | |
| 581300-U | Ascentis C18, 5 cm x 2.1 mm, 3 µm | 1 ea | 16,255 |
| 581301-U | Ascentis C18, 10 cm x 2.1 mm, 3 µm | 1 ea | 17,562 |
| 581303-U | Ascentis C18, 5 cm x 2.1 mm, 5 µm | 1 ea | 16,255 |
| 581326-U | Ascentis C18, 10 cm x 2.1 mm, 5 µm | 1 ea | 17,562 |
| 581323-U | Ascentis C18, 5 cm x 4.6 mm, 5 µm | 1 ea | 16,255 |
| 581324-U | Ascentis C18, 15 cm x 4.6 mm, 5 µm | 1 ea | 19,650 |
| Ascentis Express Fused Core HPLC Columns | | | |
| 53822-U | Ascentis Express C18, 5 x 2.1 mm, 2.7 µm | 1 ea | 22,243 |
| 53823-U | Ascentis Express C18, 10 x 2.1 mm, 2.7 µm | 1 ea | 28,104 |
| 53826-U | Ascentis Express C18, 5 x 4.6 mm, 2.7 µm | 1 ea | 22,243 |
| 53827-U | Ascentis Express C18, 10 x 4.6 mm, 2.7 µm | 1 ea | 28,104 |
| 53831-U | Ascentis Express C8, 5 x 2.1 mm, 2.7 µm | 1 ea | 22,243 |
| 53832-U | Ascentis Express C8, 10 x 2.1 mm, 2.7 µm | 1 ea | 28,104 |
| 53836-U | Ascentis Express C8, 5 x 4.6 mm, 2.7 µm | 1 ea | 22,243 |
| 53837-U | Ascentis Express C8, 10 x 4.6 mm, 2.7 µm | 1 ea | 28,104 |

Note: All Prices in Indian Rupees. Taxes & other levies extra as applicable

Sigma Aldrich Chemicals Pvt. Ltd.


#12, Bommasandra-Jigani Link Road, Bangalore - 560 100

T +91 80 6621 9600 F +91 80 6621 9650 E india@sial.com

New Delhi +91 11 4358 8000 Kolkata +91 33 4013 8000 Mumbai +91 22 4087 2364

Lucknow +91 522 400 3455 Chennai +91 44 4214 8991 Pune +91 20 2553 9079

Chandigarh +91 172 463 0255 Hyderabad +91 40 4015 5488 Ahmedabad +91 79 2754 1971



For your free copy of
Supelco Catalog,
please write to
INDMarcom@sial.com

SIAL/ANV06/0710/INR