

Suitability tests according to Ph. Eur. method 2.5.12, water semi-micro determination**Water determination by Karl Fischer titration with HYDRANAL®-Composite**

(English)	(German)
Acetone	Aceton
Calcium acetate	Calciumacetat
Citric acid anhydrous	Citronensäure wasserfrei
Citric acid monohydrate	Citronensäure Monohydrat
Dibutyl phthalate	Dibutylphthalat
Dichloromethane	Dichlormethan
Dimethyl sulfoxide	Dimethylsulfoxid
Erythromycine	Erythromycin
Ethyl acetate	Essigsäureethylester
D(-)-Fructose	D(-)-Fructose
Gentamicin Sulphate	Gentamicinsulfat
D(+)-Glucose monohydrate	D(+)-Glucose Monohydrat
D(+)-Glucose anhydrous	D(+)-Glucose wasserfrei
Glycerol	Glycerol
Lactose monohydrate	Lactose Monohydrat
Magnesium acetate tetrahydrate	Magnesiumacetat Tetrahydrat
Magnesium chloride hexahydrate	Magnesiumchlorid Hexahydrat
D-Mannitol	D-Mannitol
Methanol	Methanol
Olive oil	Olivenöl
Polysorbate 80	Polysorbat 80
Potassium citrate	Kaliumcitrat
Povidone	Povidon
2-Propanol	2-Propanol
Sodium citrate dihydrate	Natriumcitrat dihydrat
di-Sodium hydrogen phosphate dodecahydrate	Natriummonohydrogenphosphat- Dodecahydrat
Sorbitol solution 70%	Sorbit Lösung 70 %
Triglycerides, medium-chain	Triglyceride, mittelkettig
Trolamine (Triethanolamine)	Trolamin (Triethanolamin)
Xylitol	Xylit