



3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

Product Information

ECM gel from Engelbreth-Holm-Swarm mouse sarcoma

Catalog Number **E1270**
Storage Temperature $-20\text{ }^{\circ}\text{C}$

Product Description

The major classes of molecules that regulate cellular development and function include growth and differentiation factors, cell adhesion molecules, and components of the extracellular matrix (ECM). The ECM is defined as all secreted molecules that are immobilized outside of cells. However, it is not always morphologically visible. The major constituents of the ECM include collagens, non-collagenous glycoproteins, and proteoglycans.

ECM gel was prepared from Engelbreth-Holm-Swarm (EHS) sarcoma produced in mice, following a published procedure,¹ to a protein concentration of 8-12 mg/ml. ECM gel contains laminin as a major component, collagen type IV, heparan sulfate proteoglycan, entactin and other minor components. It is treated with chloroform to prevent aerobic and anaerobic microbial growth.

ECM gel will undergo thermally activated polymerization when brought to $20\text{-}40\text{ }^{\circ}\text{C}$ to form a reconstituted basement membrane. The process of gelation is reversible. Addition of collagen type IV to ECM gel increases polymerization, whereas, addition of collagen type I, fibronectin, or heparin, does not.²

PC12 cells show neurite formation within 2 days when grown on a thin layer of ECM Gel.

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Storage/Stability

Store at $-20\text{ }^{\circ}\text{C}$ for long-term storage. ECM gel may be stored at $2\text{-}8\text{ }^{\circ}\text{C}$ for up to 72 hrs.

Product Use

Thaw gel overnight at $2\text{-}8\text{ }^{\circ}\text{C}$ before use. Dispense gel to wells of a multiwell plate using pipettes, plates, etc. pre-cooled to $2\text{-}8\text{ }^{\circ}\text{C}$. For a 96 well plate, use $50\text{-}100\text{ }\mu\text{L/well}$. ECM gel also may be diluted up to twofold with cold ($2\text{-}8\text{ }^{\circ}\text{C}$) Dulbecco's Modified Eagle's Medium. Dilution may help in cases in which the product is still gelatinous in the cold. Gel dilutions should be made before it is added to the plate. ECM gel will gel within 5 minutes at $20\text{ }^{\circ}\text{C}$. For prolonged manipulations, work should be conducted below $10\text{ }^{\circ}\text{C}$.

Cells may be plated on top of a thin gel layer (0.5 mm) or cultured inside a 1 mm layer. In the latter application, cells should be added to the gel prior to plating at a recommended density of $3\text{-}4 \times 10^4$ cells per ml.

To dissociate cells from the gel, use protease (dispase) in PBS without calcium, magnesium, and EDTA, at a concentration of $0.6\text{-}2.4$ units per ml.

References

1. Kleinman, H.K. *et al.*, in Molecular and Cellular Aspects of Basement Membranes, Rohrbach, D.H. and Timpl, R., Eds. Academic Press, (1993), pp. 309-326.
2. Carey, D.J. *et al.*, *J. Cell Biol.*, **102**, 2254-2263, (1986).

NDH,PHC,LCM,MAM 10/06-1

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.