



## Product Information

### MONOCLONAL ANTI-MICROPHthalmIA CLONE C5

Purified Mouse Immunoglobulin

Product Number **M 6065**

#### Product Description

Monoclonal Anti-Microphthalmia (mouse IgG1 isotype) is derived from the hybridoma produced by the fusion of splenocytes from RBF/DnJ mice immunized with an N-terminal fragment of human microphthalmia protein and mouse myeloma NS1 cells. The antibody is purified by Protein G chromatography.

Monoclonal Anti-Microphthalmia recognizes serine phosphorylated and non-phosphorylated melanocytic isoforms of microphthalmia from human, mouse or rat. This antibody has been used in immunoblotting (doublet of 52-56 kDa), immunoprecipitation, immunohistochemistry on formalin-fixed paraffin-embedded or frozen tissue sections, and gel shift.

Microphthalmia (Mi in mouse or MITF in human) is a basic helix-loop-helix-leucine zipper (BHLH-ZIP) transcription factor. Microphthalmia is involved in the differentiation, development and survival of melanocytes and cells of the retinal pigment epithelium, i.e. cells responsible for hair, skin, and eye color.<sup>1-4</sup> It activates the expression of the melanocyte specific genes *tyrosinase* and *TRP1* (tyrosinase-related protein 1) by binding as a homo- or heterodimer to a symmetrical DNA sequence (E box) (5'-CATGTG-3') located within the M box found in their promoters.<sup>5,6</sup> Microphthalmia also appears to be involved in the differentiation mast cells, osteoclasts, basophils and natural killer cells.<sup>7,8</sup>

Microphthalmia is expressed in a limited number of cell types including heart, mast cells, osteoclast precursors, and melanocytes. There are a number of different isoforms of microphthalmia resulting from alternative splicing and alternative promoters. These isoforms differ at their amino-termini and in their expression patterns.<sup>9,10</sup>

In humans, mutations of microphthalmia cause Waardenburg Syndrome Type II, a dominantly inherited hearing loss accompanied by pigmentary disturbances.<sup>11</sup> Mutations of Mi in mouse result in profound loss of pigmented cells in the skin, eye and inner ear, as well as osteoporosis and defects in natural killer and mast cells. An osteoporotic rat strain harbors

a large genomic deletion encompassing the 3' half of microphthalmia. Osteoclasts from those animals lack microphthalmia protein.<sup>12</sup>

Immunohistochemical detection of microphthalmia transcription factor in tissues using monoclonal antibodies is a valuable tool in the identification of melanocytic lesions in numerous sites. This technique may facilitate the detection of micrometastases in sentinel lymph nodes.<sup>13</sup>

#### Reagent

Monoclonal Anti-Microphthalmia is supplied as a solution in phosphate buffered saline, pH 7.4, with 0.08% sodium azide as a preservative.

#### Precautions and Disclaimer

Due to the sodium azide content, a material safety data sheet (MSDS) for this product has been sent to the attention of the safety officer of your institution. Consult the MSDS for information regarding hazards and safe handling practices.

#### Storage/Stability

Store at -20 °C. Upon initial thawing freeze the solution in working aliquots for extended storage. Avoid repeated freezing and thawing to prevent denaturing the antibody. Do not store in a frost-free freezer. The antibody is stable for at least 12 months when stored appropriately. Working dilutions should be discarded if not used within 12 hours.

### Product Profile

A recommended working concentration of 1 µg/ml is determined by immunohistochemistry using formalin-fixed paraffin-embedded human melanoma tissue.

For immunoprecipitation and gel supershift assays, use a working concentration of 2 µg/mg of protein lysate.

501 Mel human melanoma cells or wild-type human, rat or mouse osteoclast cells may be used for positive controls.

Note: In order to obtain best results using different techniques and preparations we recommend determining optimal working concentration by titration.

### References

1. Hodgkinson, C.A., et al., *Cell*, **74**, 395-404 (1993).
2. Steingrimsson, E., et al., *Nat. Genet.*, **8**, 50-54 (1994).
3. Bertolotto, C., et al., *J. Cell Biol.*, **142**, 827-835 (1998).
4. Aberdam, E., et al., *J. Biol. Chem.*, **273**, 19560-19565 (1998).
5. Hemesath, T.J., et al., *Genes Dev.*, **8**, 2770-2780 (1994).
6. Aksan, and Goding, C.R., *Mol. Cell. Biol.*, **18**, 6930-6938 (1998).
7. Luchin, A., et al., *J. Biol. Chem.*, **276**, 36703-36710 (2001).
8. Stechschulte, D.J., et al., *J. Cell Physiol.*, **132**, 565-570 (1987).
9. Udono, T. et al., *Biochim Biophys Acta*, **1491**, 205-219 (2000).
10. Shibahara, S., et al., *J. Investig. Dermatol., Symp. Proc.*, **6**, 99-104 (2001).
11. Tassabehji, M., *Nat. Genet.*, **8**, 251-255 (1994).
12. Weilbaecher, K. N., et al., *J. Exp. Med.*, **187**, 775-785 (1998).
13. O'Reilly, F.M., et al., *J. Am. Acad. Dermatol.*, **45**, 414-419 (2001).

AH 03/02

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.