



## Product Information

### ANTI- SYNTAXIN 1

Developed in Rabbit, IgG Fraction of Antiserum

Product Number **S 1172**

#### Product Description

Anti- Syntaxin 1 is developed in rabbit using a highly purified fusion protein of GST<sup>1</sup> and a cytoplasmic part of rat syntaxin 1A<sup>2,3</sup> as immunogen. The serum was depleted of anti-GST antibodies by affinity chromatography on immobilized GST, and then the IgG fraction was isolated on immobilized protein A.

Anti- Syntaxin 1 recognizes both the 1A and 1B syntaxin proteins of rat, mouse, electric ray (*Torpedo* sp.) and crayfish by immunohistochemistry and immunoblotting.

Chemical neurotransmitters are stored within the nerve terminal in synaptic vesicles that are often found associated with cytoskeletal components or the pre-synaptic plasma membrane.<sup>3</sup> Upon nerve stimulation, activation of voltage-gated Ca<sup>2+</sup> channels in the nerve terminal plasma membrane results in an influx of Ca<sup>2+</sup>. The increase in cytosolic Ca<sup>2+</sup> concentration triggers the fusion of a portion of the synaptic vesicle population with the presynaptic plasma membrane, resulting in the neurotransmitter release. The docking and subsequent fusion of synaptic vesicles with the presynaptic plasma membrane occur at a restricted, morphologically distinct domain known as the active zone. The process of synaptic vesicle docking with the presynaptic membrane may represent the assembly of a pre-fusion complex that is likely to include components of each membrane. Three synaptic vesicle membrane proteins, synaptotagmin, synaptophysin,<sup>4</sup> and synapsin I, exhibit properties suggestive of a role in synaptic vesicle docking or fusion. Syntaxin (also cited as HPC-1 antigen),<sup>3,5</sup> a 35 kDa molecule with carboxyl-terminal membrane anchor, is a synaptic protein identified by its ability to interact with the synaptic vesicle protein synaptotagmin. It has been implicated in docking at synaptic vesicles of presynaptic neurotransmitter release sites.<sup>3,5,6</sup> The molecular machinery for secretion seems to be conserved from yeast to neurons, since three genes have been

identified in yeast that encode proteins with a carboxyl-terminal membrane anchor and significant homology to syntaxin, primarily over a 70 amino acid segment near the membrane anchor.<sup>6,7</sup> In addition, epimorphin, a protein expressed in mesenchymal cells that regulates the morphogenesis of adjacent epithelial cells, is also closely related (63% identical) to syntaxins A and B.<sup>7</sup> Antibodies reacting specifically against syntaxins are useful for studies on the molecular machinery of secretion, cellular heterogeneity, and the development of the central nervous system.

#### Reagents

Anti- Syntaxin 1 is supplied as purified IgG fraction of antiserum and is lyophilized at 1.0 mg/ml from phosphate buffered saline, pH 7.4, containing 5% sucrose and 0.025% sodium azide.

#### Precautions and Disclaimer

Due to the sodium azide content, a material safety data sheet (MSDS) for this product has been sent to the attention of the safety officer of your institution. Consult the MSDS for information regarding hazardous and safe handling practices.

#### Preparation Instructions

Reconstitute the lyophilized vial with 0.05 ml or 0.2 ml deionized water, depending on the package size purchased. Antibody dilutions should be made in buffer containing 1-3% bovine serum albumin.

#### Storage/Stability

Prior to reconstitution, store at -20 °C. After reconstitution, the stock antibody solution may be stored at 4 °C for up to 2 weeks. For extended storage, freeze in working aliquots. Repeated freezing and thawing is not recommended. Storage in "frost-free" freezers is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use. Working dilution samples should be discarded if not used within 12 hours.

### Product Profile

The recommended working dilution is 1:700 – 1:1250 (1.5 - 0.8 µg/ml) for immunoblotting using HRP-goat anti-rabbit and detection by ECL.

The recommended working dilution is 1:33 (30 µg/ml) for immunohistochemistry. Anti-Syntaxin 1 is directed against an intracellular epitope. Thus, a procedure including permeabilization of cells with 0.2% Triton X-100 is recommended.

Note: In order to obtain best results and assay sensitivities of different techniques and preparations, we recommend determining optimal working dilutions by titration test.

### References

1. Smith, D.B. and Johnson, K.S., *Gene*, **67**, 31 (1988).
2. Bennet, M.K. et al., *Science*, **257**, 255 (1992).
3. Inoue, A. and Akagawa, K., *Biochem. Biophys. Res. Commun.*, **187**, 1144 (1992).
4. Devoto, S. and Barnstable, C., *Ann. N.Y. Acad. Sci.*, **493**, 493 (1987).
5. Barinaga, M., (ed.), *Science*, **260**, 487 (1993).
6. Bennet, M. and Scheller, R., *Proc. Natl. Acad. Sci. (USA)*, **90**, 2559 (1993).
7. Hirai, Y. et al., *Cell*, **73**, 425 (1993).

mje 7/00

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.